

Overview of items



Family number	Extension Partial (T) Full (V) Over (Ü)	Max. WLL per pair in kg	Slide length in mm (retracted)	Material Steel (S) Stainless steel (ES) Aluminium (A)	Horizontal mounting	Soft- Close	Push to open	Auto- retrac- tion	Latch open	Latch closed	Quick frontal release
K1566	T	10	133 - 550	S	X					X	
K1567	T	12	222 - 328	S	X					X	
K1568	T	20	197 - 328	S	X						
K1569	Ü	30	250 - 550	S	X					X	X
K1571	V	35	300 - 700	S	X	X				X	X
K1572	V	35	300 - 700	S	X		X			X	X
K1573	V	35	300 - 690	S	X	X				X	X
K1574	V	35	300 - 700	S	X		X			X	X
K1575	V	40	270 - 700	S	X			X		X	X
K1577	V	45	250 - 700	S	X					X	X
K1710	T	50	305 - 711	S	X						
K1578	Ü	60	250 - 700	S	X					X	X
K1579	Ü	60	350 - 600	S	X					X	X
K1711	T	65	305 - 711	S	X				X		X
K1712	T	65	300 - 700	ES	X					X	
K1713	Ü	70	305 - 711	S	X				X		X
K1714	Ü	70	305 - 711	ES	X				X		X

Overview of items



Family number	Extension Partial (T) Full (V) Over (Ü)	Max. WLL per pair in kg	Slide length in mm (retracted)	Material Steel (S) Stainless steel (ES) Aluminium (A)	Horizontal mounting	Soft- Close	Push to open	Auto- retraction	Latch open	Latch closed	Quick frontal release
K1715	V	80	300 - 700	ES	X					X	
K1716	Ü	90	305 - 660	ES	X				X		X
K1580	Ü	90	300 - 700	S	X					X	X
K1581	V	136	310 - 910	S	X					X	
K1717	V	160	305 - 914	S	X					X	X
K1718	Ü	160	300 - 1100	S						X	
K1719	V	227	305 - 1524	S					X	X	
K1720	V	272	254 - 1524	S	X						
K1721	V	300	300 - 1000	A							