

Tension levers stainless steel with internal thread, 20°

Item description/product images



Description

Material:

Steel parts stainless steel 1.4305.

Ball knob black plastic.

Version:

Stainless steel parts bright.

Ball knob polished.

Note:

Tension levers can be used for simple clamping or control operations.

Where applicable, there must be enough space available so that the grip can be rotated 360°.

Overview of items

Order No.	Thread type	Form	Size	X	T	D	D1	D2	H	H2	A
K1444.208	internal thread	20°	1	M8	18	24	10	25	40	32,5	84,5
K1444.210	internal thread	20°	1	M10	18	24	10	25	40	32,5	84,5
K1444.2101	internal thread	20°	2	M10	20	28	12	32	46	36,5	100
K1444.212	internal thread	20°	2	M12	20	28	12	32	46	36,5	100
K1444.216	internal thread	20°	3	M16	23	33	13	32	52	41	121
K1444.220	internal thread	20°	4	M20	26	41	13	32	61	49	123