

Telescopic slides, stainless steel for side mounting, partial extension, load capacity up to 65 kg

Item description/product images



Description

Material:

Slides stainless steel 1.4301.

Ball cage stainless steel 1.4301.

Balls stainless steel 1.4034.

Version:

Slides bright.

Ball cages bright.

Balls bright.

Note for ordering:

Sold in pairs.

Note:

On telescopic slides with partial extension, the travel is less than the installed length. Latches in closed position.

The dynamic load capacity of the telescopic slides indicates the maximum load rating of a vertically mounted slide pair when the entire extension length is used. The load capacity specified is calculated with a slide spacing of 450 mm and is based on the maximum value with 10,000 or 80,000 cycles.

The load capacity is ca. 75% lower by horizontal mounting.

The head height of the fastening screws should not exceed 2.5 mm otherwise there is a risk of collision with other parts of the slide.


Advantages:

Latches in closed position

Suitable for flat mounting

Light running

Drawings



Telescopic slides, stainless steel for side mounting, partial extension, load capacity up to 65 kg

Overview of items

Stainless steel telescopic slides for side mounting, partial extension, load capacity up to 65 kg

Order No.	Assembly	Product type	Load capacity per pair (80,000 cycles) kg	Loading pair (10,000 cycles) kg	Packaging type
K1712.0300	side mounting	standard	60	65	1 piece = 1 pair
K1712.0350	side mounting	standard	57	63	1 piece = 1 pair
K1712.0400	side mounting	standard	54	59	1 piece = 1 pair
K1712.0450	side mounting	standard	50	57	1 piece = 1 pair
K1712.0500	side mounting	standard	47	53	1 piece = 1 pair
K1712.0550	side mounting	standard	45	50	1 piece = 1 pair
K1712.0600	side mounting	standard	43	46	1 piece = 1 pair
K1712.0650	side mounting	standard	41	43	1 piece = 1 pair
K1712.0700	side mounting	standard	40	42	1 piece = 1 pair

Order No.	A	A1	A2	A3	A4	A5	A6	A7	A8	B	H	Travel S	L
K1712.0300	18	32	-	-	224	256	128	160	17,5	9,5	35,34	209	300
K1712.0350	36	32	160	192	256	288	160	192	35,5	9,5	35,34	245	350
K1712.0400	22	32	160	192	320	352	160	192	21,5	9,5	35,34	282	400
K1712.0450	8	32	224	256	384	416	224	256	7,5	9,5	35,34	320	450
K1712.0500	26	32	224	256	416	448	224	256	25,5	9,5	35,34	357	500
K1712.0550	12	32	288	320	480	512	288	320	11,5	9,5	35,34	394	550
K1712.0600	30	32	288	320	512	544	288	320	29,5	9,5	35,34	432	600
K1712.0650	16	32	352	384	576	608	352	384	15,5	9,5	35,34	469	650
K1712.0700	34	32	352	384	608	640	352	384	33,5	9,5	35,34	506	700