

HeliCoil®plus threaded inserts

Item description/product images



Description

Material:

Stainless steel 1.4301

Version:

Green

Note:

HeliCoil®plus threaded inserts are indispensable aids for every metalworking establishment and repair workshop.

Tapped holes that have been damaged, rusted solid or drilled too big can be restored to their original size and condition within minutes.

Technically flawless and infinitely durable, resistant to corrosive influences and thermal stress. They therefore enable the repair and recovery of expensive products. The high surface finish ensures optimum yield strength and higher tensile force for high-strength screws.

HeliCoil®plus threaded inserts are also ideally suited for motion threads in all light-alloys and castings.

On request:

Other dimensions.

before



after



Overview of items

HeliCoil®plus thread inserts

Order No.	Version	Threaded Inserts	Insert length assembled mm
K2423.0521	threaded inserts	M5	5
K2423.0531	threaded inserts	M5	7,5
K2423.0541	threaded inserts	M5	10
K2423.0621	threaded inserts	M6	6
K2423.0631	threaded inserts	M6	9
K2423.0641	threaded inserts	M6	12
K2423.0821	threaded inserts	M8	8
K2423.0831	threaded inserts	M8	12
K2423.0841	threaded inserts	M8	16
K2423.1021	threaded inserts	M10	10
K2423.1031	threaded inserts	M10	15
K2423.1041	threaded inserts	M10	20
K2423.1221	threaded inserts	M12	12
K2423.1231	threaded inserts	M12	18
K2423.1241	threaded inserts	M12	24