

Ratchet levers with square socket

Item description/product images



Description

Material:

Housing carbon steel, tension nut and tension pin case-hardened steel.

Version:

Black oxidised.

Matt-finished or high-polish chrome-plated versions available at extra charge.

Note:

Tension Pin A standard version (for ratchet action):

Use for clamping and releasing in limited space and when considerable travel is involved. In order to change the tightening direction, the handle must be reversed by 180°.

Tension Pin B special version:

Use for clamping and releasing in limited space and when short travel is involved.

The handle is not reversed in order to change the tightening direction. It must be pulled out before it can be engaged in the next slot.

Clamp with H7 reamed hole and DIN 6885/1 keyway.


On request:

Other thread, reamed hole and square socket sizes.

Dimension "A" available in other lengths at extra charge.

Special version: Tension pin B.

Drawings



Ratchet levers with square socket

Overview of items

Order No.	Kind of fastening	SW	Size	A=Handle length	A2	D	D1	D2	D3	D4	H	H1	H2	H3	No. of index slots
K0128.510	square socket	10	1	150	48	22	33	17	22	36	31	4,5	15,5	3	7
K0128.512	square socket	12	1	150	48	22	33	17	22	36	31	4,5	15,5	3	7
K0128.513	square socket	13	2	180	54	27	38	20	26	43	38	6	19	4	8
K0128.514	square socket	14	2	180	54	27	38	20	26	43	38	6	19	4	8
K0128.517	square socket	17	3	230	70	35	45	24	30	51	42	6	21	4	8
K0128.519	square socket	19	4	300	80	42	56	28	35	61	47	6	23,5	4	9
K0128.520	square socket	20	4	300	80	42	56	28	35	61	47	6	23,5	4	9
K0128.522	square socket	22	4	300	80	42	56	28	35	61	47	6	23,5	4	9
K0128.524	square socket	24	4	300	80	42	56	28	35	61	47	6	23,5	4	9
K0128.530	square socket	30	5	400	110	60	75	32	38	82	53	7,5	26,5	5	11
K0128.532	square socket	32	5	400	110	60	75	32	38	82	53	7,5	26,5	5	11