## Technical information, tubular handles, with electric switch function





Туре	K1529.180	K1529.1180
Emergency stop		
(2 NC contacts)		(9) (11) 
	without	l ⊢¬- Ţ- Ţ
		' ' ( (
		(10) (12)
Push button		
(1 changeover contact)	(1) (3)	(1) (3)
( cominger of the control of the con	<u> </u>	<u> </u>
	<u> </u>	<u> </u>
	(2)	(2)
	(2)	(2)
Red/green LED	(5) (7)	(5) (7)
	LED H LED H	LED H LED H
	red green	red green
	Ĭ , , , , , , , , , , , , , , , , , , ,	Ĭ, , , , , , , , , , , , , , , , , , ,
	(6)	(6)
Emergency stop		1–42 V AC/DC
	-	max. 100 mA
Push button	24 V A	AC/DC
	max. 1.5 A	
LED operating voltage	24 \	/ DC
Connection type	8-pin / M12x1	12-pin / M12x1
Pin assignment		
(view from connector side)	2	2 10 0
	3(0.0)	3((O, O, O)) <sup>9</sup>
		11 0 0 8 12
	4 0 6	
	'5	6
	1) White (WH)	1) Brown (BN)
	2) Brown (BN)	2) Blue (BU)
	3) Green (GN)	3) White (WH)
	4) Yellow (YE)	4) Green (GN)
	5) Grey (GY)	5) Pink (PK)
	6) Pink (PK)	6) Yellow (YE)
	7) Blue (BU)	7) Black (BK)
	8) Red (RD)	8) Grey (GY)
		9) Red (RD)
		10) Violet (VT)
		11) Grey-Pink (GY/PK)
		12) Red-Blue (RD/BU)