

Screwed-down floor version

Item description/product images



Description

Material:

Aluminium profile.
Acrylic glass.

Version:

Square profile.
Acrylic glass panel.

Note:

Total height: 1886 mm
Width: 900 mm
Foot surface each: 72x60 mm

Table and floor standing versions consisting of an aluminium frame and acrylic glass panels.

Stable construction and universally applicable.

Square profile, frame top open.

Acrylic glass 850 x 850 mm (4 mm thick).

Total clearance height 1000 mm.

Pass-through clearance 140 mm by a table height of 860 mm.

Application:

Retail shops / pharmacies

Grocery stores / checkout areas

Medical practices / waiting rooms

Reception counters / entrance area

On request:

Special sizes.

Overview of items

Screwed-down floor version

Order No.	Item
K1081.22	Floor version