

Adjustable supports

Item description/product images




Description

Material:
Carbon steel.

Version:
black oxidised.
Threaded pin tempered

Note:
Inserts K0826 can be mounted in the top to suit the application.

Drawings



Overview of items

Adjustable supports

Adjustable supports

Overview of items

Order No.	A min.	B max.	C	D	SW	SW1	G	G1
K0825.06040	40	10	20	27	24	24	M6	M16X1,5
K0825.06050	50	20	20	27	24	24	M6	M16X1,5
K0825.08040	40	10	20	27	24	24	M8	M16X1,5
K0825.08050	50	20	20	27	24	24	M8	M16X1,5
K0825.08070	70	40	20	27	24	24	M8	M16X1,5
K0825.10040	40	10	25	40	36	30	M10	M20x1,5
K0825.10050	50	20	25	40	36	30	M10	M20x1,5
K0825.10070	70	40	25	40	36	30	M10	M20x1,5
K0825.12040	40	10	30	40	36	30	M12	M20x1,5
K0825.12050	50	20	30	40	36	30	M12	M20x1,5
K0825.12070	70	40	30	40	36	30	M12	M20x1,5
K0825.12100	100	50	30	50	46	36	M12	M24x2
K0825.12150	150	100	30	50	46	36	M12	M24x2
K0825.16040	40	10	30	40	36	30	M16	M20x1,5
K0825.16050	50	20	30	40	36	30	M16	M20x1,5
K0825.16070	70	40	30	40	36	30	M16	M20x1,5
K0825.16100	100	50	30	50	46	36	M16	M24x2
K0825.16150	150	100	30	50	46	36	M16	M24x2