

드릴 직경(mm)의 마찰 토크(Nm)

크기	3	4	6	8	10	12	14	15	16	18	19	20	24	25	28	30	32	35	38	40	42	45	48	50	55
7	1.2	1.3	1.5																						
9		2.3	2.5	2.8	3.0																				
12		6.6	6.9	7.4	8.0	8.6																			
14			14	14.7	15.7	16.7	17.7	18.3	18.8																
19				42	44	47	49	50	51	54	55	56													
24					58	61	63	64	65	67	69	70	74	76	79	81	84								
28							105	107	109	112	114	116	123	124	130	133	137	142	147						
38								241	244	251	254	258	271	274	284	291	297	307	317	324	330	340	350		
42												433	452	457	471	481	491	505	519	529	539	553	568	577	
48												452	471	476	491	500	510	524	539	548	558	572	587	596	620