

## Tension levers stainless steel with internal thread, 0°

### Item description/product images



### Description

#### Material:

Steel parts stainless steel 1.4305.

Ball knob black plastic.

#### Version:

Stainless steel parts bright.

Ball knob polished.

#### Note:

Tension levers can be used for simple clamping or control operations.

Where applicable, there must be enough space available so that the grip can be rotated 360°.

### Overview of items

Order No.	Thread type	Form	Size	X	T	D	D1	D2	H	H2	A
K1444.2082	internal thread	0°	1	M8	18	24	10	25	40	32,5	88,1
K1444.2102	internal thread	0°	1	M10	18	24	10	25	40	32,5	88,1
K1444.21012	internal thread	0°	2	M10	20	28	12	32	46	36,5	104
K1444.2122	internal thread	0°	2	M12	20	28	12	32	46	36,5	104
K1444.2162	internal thread	0°	3	M16	23	33	13	32	52	41	126,5
K1444.2202	internal thread	0°	4	M20	26	41	13	32	61	49	128,5