

Recessed handles, aluminium, fold-down, mounted via rubber profile



Item description/product images

19"



Description

Material:

Tray and folding handle in aluminium profile, end caps polyamide; form A: mounting by rubber insert

Version:

Tray and grip glass-bead blasted, satin finish and anodised black or natural colour. Rubber profile black.

Fastening screws electro zinc-plated.

Note:

Profile Folding Handles form A can be fitted without screw mounting with 2 soft plastic profiles with sheet strengths of 1-2.5 mm.

Two cross-slots for M4 screws allow earth/ground connection and can serve as a mounting aid for additional add-on parts.

Assembly:

After fitting the lower rubber profile, press the two side caps onto the handle. Next press the handle over the lower edge of the mounting cutout at a 45° angle and then push it up against the housing panel.


Now push the 2nd rubber profile into the upper groove or fix in place with 2 countersunk screws.



Recessed handles, aluminium, fold-down, mounted via rubber profile



Drawings



Overview of items

Profile Folding Handles

Order No.	Main colour	Form	Version 2	Н	L	L1	T	Mounting cutout	Load capacity N
K0239.10011	black	А	plug-in	90	100	115	19,5	107 x 73	500
K0239.11811	black	Α	plug-in	90	118	133	19,5	125 x 73	500
K0239.16711	black	Α	plug-in	90	167	182	19,5	174 x 73	500
K0239.10013	natural	Α	plug-in	90	100	115	19,5	107 x 73	500
K0239.11813	natural	Α	plug-in	90	118	133	19,5	125 x 73	500
K0239.16713	natural	Α	plug-in	90	167	182	19,5	174 x 73	500



Recessed handles, aluminium, fold-down, mounted via rubber profile



Overview of items