

## Filler necks

### Item description/product images



### Description

#### Material, version:


1. Filler housing chrome steel
2. Air filter polyurethane (PU foam), filter mesh 40 µm. Flow rate up to 720 l/min
3. Flat seal cork
4. Mounting flange with fastening screws, bayonet fitting
5. Flat seal cork
6. Chain nickel-plated brass
7. Filler sieve electro zinc-plated steel

#### Note:

The filler necks are supplied with seals and M5 fastening screws.

Not suitable for water tanks.

### Drawings



## Filler necks

### Overview of items

---

#### Filler necks

Order No.	Version 1	D	D1	D2	D3	D4	D5	L	L1
K0471.45	without chain	46,5	27,5	52	25	41,3	6 (3x)	43	66
K0471.77	with chain	80	49	83	44	71,5	6 (6x)	57	80