



Knurled knobs Form L, with external thread

Item description/product images




Description

Material:
Black grey thermoplastic.
Threaded pin steel 5.8.

Version:
Steel trivalent blue-passivated.

Drawings



Overview of items

Knurled knobs Form L, with external thread

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	L
K0260.5105X10	L	black grey RAL 7021	1	M5	40	16,5	31	13	10
K0260.51051X10	L	orange RAL 2004	1	M5	40	16,5	31	13	10
K0260.51052X10	L	signal green RAL6032	1	M5	40	16,5	31	13	10
K0260.51053X10	L	blue RAL5017	1	M5	40	16,5	31	13	10

Knurled knobs Form L, with external thread

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	L
K0260.51055X10	L	light grey RAL 7035	1	M5	40	16,5	31	13	10
K0260.51056X10	L	traffic red RAL 3020	1	M5	40	16,5	31	13	10
K0260.51057X10	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	10
K0260.5105X20	L	black grey RAL 7021	1	M5	40	16,5	31	13	20
K0260.51051X20	L	orange RAL 2004	1	M5	40	16,5	31	13	20
K0260.51052X20	L	signal green RAL6032	1	M5	40	16,5	31	13	20
K0260.51053X20	L	blue RAL5017	1	M5	40	16,5	31	13	20
K0260.51055X20	L	light grey RAL 7035	1	M5	40	16,5	31	13	20
K0260.51056X20	L	traffic red RAL 3020	1	M5	40	16,5	31	13	20
K0260.51057X20	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	20
K0260.5105X40	L	black grey RAL 7021	1	M5	40	16,5	31	13	40
K0260.51051X40	L	orange RAL 2004	1	M5	40	16,5	31	13	40
K0260.51052X40	L	signal green RAL6032	1	M5	40	16,5	31	13	40
K0260.51053X40	L	blue RAL5017	1	M5	40	16,5	31	13	40
K0260.51055X40	L	light grey RAL 7035	1	M5	40	16,5	31	13	40
K0260.51056X40	L	traffic red RAL 3020	1	M5	40	16,5	31	13	40
K0260.51057X40	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	40
K0260.5106X10	L	black grey RAL 7021	1	M6	40	16,5	31	13	10
K0260.51061X10	L	orange RAL 2004	1	M6	40	16,5	31	13	10
K0260.51062X10	L	signal green RAL6032	1	M6	40	16,5	31	13	10
K0260.51063X10	L	blue RAL5017	1	M6	40	16,5	31	13	10
K0260.51065X10	L	light grey RAL 7035	1	M6	40	16,5	31	13	10
K0260.51066X10	L	traffic red RAL 3020	1	M6	40	16,5	31	13	10
K0260.51067X10	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	10
K0260.5106X20	L	black grey RAL 7021	1	M6	40	16,5	31	13	20
K0260.51061X20	L	orange RAL 2004	1	M6	40	16,5	31	13	20
K0260.51062X20	L	signal green RAL6032	1	M6	40	16,5	31	13	20
K0260.51063X20	L	blue RAL5017	1	M6	40	16,5	31	13	20
K0260.51065X20	L	light grey RAL 7035	1	M6	40	16,5	31	13	20
K0260.51066X20	L	traffic red RAL 3020	1	M6	40	16,5	31	13	20
K0260.51067X20	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	20
K0260.5106X40	L	black grey RAL 7021	1	M6	40	16,5	31	13	40
K0260.51061X40	L	orange RAL 2004	1	M6	40	16,5	31	13	40
K0260.51062X40	L	signal green RAL6032	1	M6	40	16,5	31	13	40
K0260.51063X40	L	blue RAL5017	1	M6	40	16,5	31	13	40
K0260.51065X40	L	light grey RAL 7035	1	M6	40	16,5	31	13	40
K0260.51066X40	L	traffic red RAL 3020	1	M6	40	16,5	31	13	40
K0260.51067X40	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	40
K0260.5108X15	L	black grey RAL 7021	1	M8	40	16,5	31	13	15
K0260.51081X15	L	orange RAL 2004	1	M8	40	16,5	31	13	15
K0260.51082X15	L	signal green RAL6032	1	M8	40	16,5	31	13	15
K0260.51083X15	L	blue RAL5017	1	M8	40	16,5	31	13	15
K0260.51085X15	L	light grey RAL 7035	1	M8	40	16,5	31	13	15
K0260.51086X15	L	traffic red RAL 3020	1	M8	40	16,5	31	13	15
K0260.51087X15	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	15
K0260.5108X30	L	black grey RAL 7021	1	M8	40	16,5	31	13	30
K0260.51081X30	L	orange RAL 2004	1	M8	40	16,5	31	13	30
K0260.51082X30	L	signal green RAL6032	1	M8	40	16,5	31	13	30
K0260.51083X30	L	blue RAL5017	1	M8	40	16,5	31	13	30
K0260.51085X30	L	light grey RAL 7035	1	M8	40	16,5	31	13	30
K0260.51086X30	L	traffic red RAL 3020	1	M8	40	16,5	31	13	30
K0260.51087X30	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	30
K0260.5108X60	L	black grey RAL 7021	1	M8	40	16,5	31	13	60
K0260.51081X60	L	orange RAL 2004	1	M8	40	16,5	31	13	60
K0260.51082X60	L	signal green RAL6032	1	M8	40	16,5	31	13	60
K0260.51083X60	L	blue RAL5017	1	M8	40	16,5	31	13	60
K0260.51085X60	L	light grey RAL 7035	1	M8	40	16,5	31	13	60
K0260.51086X60	L	traffic red RAL 3020	1	M8	40	16,5	31	13	60
K0260.51087X60	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	60
K0260.5208X15	L	black grey RAL 7021	2	M8	50	18	36	15	15
K0260.52081X15	L	orange RAL 2004	2	M8	50	18	36	15	15
K0260.52082X15	L	signal green RAL6032	2	M8	50	18	36	15	15

Knurled knobs Form L, with external thread

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	L
K0260.52083X15	L	blue RAL5017	2	M8	50	18	36	15	15
K0260.52085X15	L	light grey RAL 7035	2	M8	50	18	36	15	15
K0260.52086X15	L	traffic red RAL 3020	2	M8	50	18	36	15	15
K0260.52087X15	L	colza yellow RAL 1021	2	M8	50	18	36	15	15
K0260.5208X30	L	black grey RAL 7021	2	M8	50	18	36	15	30
K0260.52081X30	L	orange RAL 2004	2	M8	50	18	36	15	30
K0260.52082X30	L	signal green RAL6032	2	M8	50	18	36	15	30
K0260.52083X30	L	blue RAL5017	2	M8	50	18	36	15	30
K0260.52085X30	L	light grey RAL 7035	2	M8	50	18	36	15	30
K0260.52086X30	L	traffic red RAL 3020	2	M8	50	18	36	15	30
K0260.52087X30	L	colza yellow RAL 1021	2	M8	50	18	36	15	30
K0260.5208X60	L	black grey RAL 7021	2	M8	50	18	36	15	60
K0260.52081X60	L	orange RAL 2004	2	M8	50	18	36	15	60
K0260.52082X60	L	signal green RAL6032	2	M8	50	18	36	15	60
K0260.52083X60	L	blue RAL5017	2	M8	50	18	36	15	60
K0260.52085X60	L	light grey RAL 7035	2	M8	50	18	36	15	60
K0260.52086X60	L	traffic red RAL 3020	2	M8	50	18	36	15	60
K0260.52087X60	L	colza yellow RAL 1021	2	M8	50	18	36	15	60
K0260.5210X20	L	black grey RAL 7021	2	M10	50	18	36	15	20
K0260.52101X20	L	orange RAL 2004	2	M10	50	18	36	15	20
K0260.52102X20	L	signal green RAL6032	2	M10	50	18	36	15	20
K0260.52103X20	L	blue RAL5017	2	M10	50	18	36	15	20
K0260.52105X20	L	light grey RAL 7035	2	M10	50	18	36	15	20
K0260.52106X20	L	traffic red RAL 3020	2	M10	50	18	36	15	20
K0260.52107X20	L	colza yellow RAL 1021	2	M10	50	18	36	15	20
K0260.5210X30	L	black grey RAL 7021	2	M10	50	18	36	15	30
K0260.52101X30	L	orange RAL 2004	2	M10	50	18	36	15	30
K0260.52102X30	L	signal green RAL6032	2	M10	50	18	36	15	30
K0260.52103X30	L	blue RAL5017	2	M10	50	18	36	15	30
K0260.52105X30	L	light grey RAL 7035	2	M10	50	18	36	15	30
K0260.52106X30	L	traffic red RAL 3020	2	M10	50	18	36	15	30
K0260.52107X30	L	colza yellow RAL 1021	2	M10	50	18	36	15	30
K0260.5210X60	L	black grey RAL 7021	2	M10	50	18	36	15	60
K0260.52101X60	L	orange RAL 2004	2	M10	50	18	36	15	60
K0260.52102X60	L	signal green RAL6032	2	M10	50	18	36	15	60
K0260.52103X60	L	blue RAL5017	2	M10	50	18	36	15	60
K0260.52105X60	L	light grey RAL 7035	2	M10	50	18	36	15	60
K0260.52106X60	L	traffic red RAL 3020	2	M10	50	18	36	15	60
K0260.52107X60	L	colza yellow RAL 1021	2	M10	50	18	36	15	60
K0260.5310X20	L	black grey RAL 7021	3	M10	63	22	41	17	20
K0260.53101X20	L	orange RAL 2004	3	M10	63	22	41	17	20
K0260.53102X20	L	signal green RAL6032	3	M10	63	22	41	17	20
K0260.53103X20	L	blue RAL5017	3	M10	63	22	41	17	20
K0260.53105X20	L	light grey RAL 7035	3	M10	63	22	41	17	20
K0260.53106X20	L	traffic red RAL 3020	3	M10	63	22	41	17	20
K0260.53107X20	L	colza yellow RAL 1021	3	M10	63	22	41	17	20
K0260.5310X30	L	black grey RAL 7021	3	M10	63	22	41	17	30
K0260.53101X30	L	orange RAL 2004	3	M10	63	22	41	17	30
K0260.53102X30	L	signal green RAL6032	3	M10	63	22	41	17	30
K0260.53103X30	L	blue RAL5017	3	M10	63	22	41	17	30
K0260.53105X30	L	light grey RAL 7035	3	M10	63	22	41	17	30
K0260.53106X30	L	traffic red RAL 3020	3	M10	63	22	41	17	30
K0260.53107X30	L	colza yellow RAL 1021	3	M10	63	22	41	17	30
K0260.5310X60	L	black grey RAL 7021	3	M10	63	22	41	17	60
K0260.53101X60	L	orange RAL 2004	3	M10	63	22	41	17	60
K0260.53102X60	L	signal green RAL6032	3	M10	63	22	41	17	60
K0260.53103X60	L	blue RAL5017	3	M10	63	22	41	17	60
K0260.53105X60	L	light grey RAL 7035	3	M10	63	22	41	17	60
K0260.53106X60	L	traffic red RAL 3020	3	M10	63	22	41	17	60
K0260.53107X60	L	colza yellow RAL 1021	3	M10	63	22	41	17	60
K0260.5312X30	L	black grey RAL 7021	3	M12	63	22	41	17	30
K0260.53121X30	L	orange RAL 2004	3	M12	63	22	41	17	30

Knurled knobs Form L, with external thread

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	L
K0260.53122X30	L	signal green RAL6032	3	M12	63	22	41	17	30
K0260.53123X30	L	blue RAL5017	3	M12	63	22	41	17	30
K0260.53125X30	L	light grey RAL 7035	3	M12	63	22	41	17	30
K0260.53126X30	L	traffic red RAL 3020	3	M12	63	22	41	17	30
K0260.53127X30	L	colza yellow RAL 1021	3	M12	63	22	41	17	30
K0260.5312X60	L	black grey RAL 7021	3	M12	63	22	41	17	60
K0260.53121X60	L	orange RAL 2004	3	M12	63	22	41	17	60
K0260.53122X60	L	signal green RAL6032	3	M12	63	22	41	17	60
K0260.53123X60	L	blue RAL5017	3	M12	63	22	41	17	60
K0260.53125X60	L	light grey RAL 7035	3	M12	63	22	41	17	60
K0260.53126X60	L	traffic red RAL 3020	3	M12	63	22	41	17	60
K0260.53127X60	L	colza yellow RAL 1021	3	M12	63	22	41	17	60