

Tongue for quarter-turn lock

Item description/product images




Description

Material:
Stainless steel 1.4301.

Version:
Bright.

Drawings



Overview of items

Tongue for quarter-turn locks

Order No.	A=Tongue spacing	A for housing length H=30	A for housing length H=36	A for housing length H=40	A for housing length H=50	A for housing length H=60	L
K1340.45060	6	18	24	28	38	48	45
K1340.45080	8	20	26	30	40	50	45
K1340.45100	10	22	28	32	42	52	45
K1340.45140	14	26	32	36	46	56	45
K1340.45160	16	28	34	38	48	58	45
K1340.45180	18	30	36	40	50	60	45
K1340.45200	20	32	38	42	52	62	45
K1340.45220	22	34	40	44	54	64	45
K1340.45240	24	36	42	46	56	66	45
K1340.45260	26	38	44	48	58	68	45
K1340.45280	28	40	46	50	60	70	45
K1340.45320	32	44	50	54	64	74	45
K1340.45500	50	62	68	72	82	92	45

