

Connectors with screw fitting, Form G



Item description/product images



05

Description

Material:

TPU housing. PUR cable sheath. Brass knurled nut. Bronze contacts.

Version:

Tin-plated knurled nut. Gold-plated contacts. Number of pins: 5-pin A-encoded. screened.

Note:

Connectors with screw fitting. Connector moulded to cable.

Cable, PVC-, silicon- and halogen-free.

Drag-chain suitable.

Accessory for toggle clamp with force sensor K1463.

Technical data:

Cross-section: $5 \times 0.34 \text{ mm}^2$ Voltage: U max. 60 VElectric current: I max. 4 AInsulation resistance: $> 16\Omega$ Number of plug cycles: max. 100Degree of contamination: 3Degree of protection: IP67

Application:

Connectors with screw fitting and cable serve as a connection cable for sensors and actuators.

The cable screening protects from outside interference and ensures error-free signal transmission.

Temperature range:

Fixed: -50 °C to +80°C Moving: -25 °C to +80°C Drag chain: -25 °C to +80°C

Drawing reference:

1) Bush, 2) plug

1 = brown (BN)

2 = white (WH)

3 = blue (BU)

4 = black (BK)


5 = grey(GY)



Connectors with screw fitting, Form G



Drawings



Overview of items

Order No.	Form	B1	B2	D1	D2	D3	G1	G2	H1	H2	L1	L2	Р	No. of conductors x conductor cross-section
K1482.1221245X1000	G	15,5	15,5	14,5	14,5	6	M12X1	M12X1	28,35	32,05	38,25	38,25	1000	5X0,34 mm ²
K1482.1221245X5000	G	15,5	15,5	14,5	14,5	6	M12X1	M12X1	28,35	32,05	38,25	38,25	5000	5X0,34 mm²