

Swivel and fixed castors standard version

Item description/product images



Description

Material:

Housing steel plate.

Wheel body PA 6 with vulcanised elastic solid rubber tyre.

Version:

Housing press formed.

Double ball bearing with ball shield in castor head.

Roller bearings in the wheels.


Note:

Wheel axle bolted.

Wheels are shock and impact proof.

Swivel and fixed castors standard version

Drawings



Overview of items

Swivel and fixed castors standard version

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
K1762.100371	Fixed castor	without locking system	roller bearing	-	32	-	60	85	100	9	125	100	80	-	170
K1762.125371	Fixed castor	without locking system	roller bearing	-	37	-	60	85	125	9	150	100	80	-	200
K1762.160501	Fixed castor	without locking system	roller bearing	-	50	75	80	110	160	11	195	140	105	-	350

Swivel and fixed castors standard version

Overview of items

Order No.	Item	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	R	Permissible load kg
K1762.200501	Fixed castor	without locking system	roller bearing	-	50	75	80	110	200	11	235	140	105	-	400
K1762.10037	Swivel castor	without locking system	roller bearing	36	32	-	60	85	100	9	125	100	80	86	170
K1762.12537	Swivel castor	without locking system	roller bearing	40	37	-	60	85	125	9	150	100	80	102,5	200
K1762.16050	Swivel castor	without locking system	roller bearing	60	50	75	80	110	160	11	195	140	105	140	350
K1762.20050	Swivel castor	without locking system	roller bearing	65	50	75	80	110	200	11	235	140	105	165	400
K1762.100372	Swivel castor	with stop-fix locking system	roller bearing	36	32	-	60	85	100	9	125	100	80	86	170
K1762.125372	Swivel castor	with stop-fix locking system	roller bearing	40	37	-	60	85	125	9	150	100	80	102,5	200
K1762.160502	Swivel castor	with stop-fix locking system	roller bearing	60	50	75	80	110	160	11	195	140	105	140	350
K1762.200502	Swivel castor	with stop-fix locking system	roller bearing	65	50	75	80	110	200	11	235	140	105	165	400