

Overview of items

Family number	Extension Partial (T) Full (V) Over (Ü)	Max. WLL per pair in kg	Slide length in mm (retracted)	Material Steel (S) Stainless steel (ES) Aluminium (A)	Horizontal mounting	Mounting bracket	Soft- Close	Push to open	Auto- retraction	Latch open	Latch closed	Quick frontal release
K1566	T	10	133 - 550	S	X						X	
K1567	T	12	222 - 328	S	X						X	
K1568	T	20	197 - 328	S	X							
K2089	T	20	200 - 500	S	X							X
K2090	V	30	200 - 600	S								
K1569	Ü	30	250 - 550	S	X						X	X
K1571	V	35	300 - 700	S	X		X				X	X
K1572	V	35	300 - 700	S	X			X			X	X
K1573	V	35	300 - 690	S	X		X				X	X
K1574	V	35	300 - 700	S	X			X			X	X
K1575	V	40	270 - 700	S	X				X		X	X
K1577	V	45	250 - 700	S	X						X	X
K1710	T	50	305 - 711	S	X	K2095						
K1578	Ü	60	250 - 700	S	X						X	X
K1579	Ü	60	350 - 600	S	X						X	X
K1711	T	65	305 - 711	S	X	K2095				X		X
K1712	T	65	300 - 700	ES	X	K2096					X	
K2087	V	68	250 - 700	S							X	X
K2088	V	68	300 - 700	S					X		X	X
K2091	Ü	68	305 - 711	S	X					X	X	X
K1713	Ü	70	305 - 711	S	X	K2095				X		X
K1714	Ü	70	305 - 711	ES	X					X		X
K1715	V	80	300 - 700	ES	X						X	
K2092	Ü	90	300 - 790	ES								X
K1716	Ü	90	305 - 660	ES	X					X		X
K1580	Ü	90	300 - 700	S	X						X	X
K1581	V	136	310 - 910	S	X						X	
K1717	V	160	305 - 914	S	X	K2093					X	X
K1718	Ü	160	300 - 1100	S		K2094 K2095						X
K1719	V	227	305 - 1524	S		K2093				X	X	
K1720	V	272	254 - 1524	S	X	K2093						
K1721	V	300	300 - 1000	A								