

## Star grips similar to DIN 6336, stainless steel, Form B, drilled through



### Item description/product images





## **Description**

#### **Material:**

Stainless steel 1.4308.


#### **Version:**


Ground and polished or blasted.

#### On request:

With external thread.

#### **Drawings**





#### **Overview of items**

#### Star Grips in stainless steel, similar to DIN 6336

Order No.	Form	Surface finish body	D	D1	D2	Н	Н3
K0150.232062	В	polished	6	32	12	21	10
K0150.240082	В	polished	8	40	14	26	13
K0150.250102	В	polished	10	50	18	34	17
K0150.263122	В	polished	12	63	20	42	21
K0150.232063	В	blasted	6	32	12	21	10
K0150.240083	В	blasted	8	40	14	26	13
K0150.250103	В	blasted	10	50	18	34	17
K0150.263123	В	blasted	12	63	20	42	21

1/2



# Star grips similar to DIN 6336, stainless steel, Form B, drilled through



Overview of items