

Handwheels 2-spoke plastic, with folding grip

Item description/product images



Description

Material:

Handwheel, reinforced and stabilised polyamide.

Centre caps, polyamide.

Centre bush and tapped insert for cylinder grip, steel.

Version:

Handwheel, oil and grease resistant, black (RAL 9011), satin finish.

Centre caps, grey (RAL 7035).


Centre bush and taped insert for folding grip, black oxidised.

On request:

Other cap colours.

Special versions.

Drawings



Overview of items

Handwheels 2-spoke, plastic, with folding grip

Handwheels 2-spoke plastic, with folding grip

Overview of items

Order No.	Version 1	D1	D2	D3	D4	A	H	L	L1	L2	L3	L4	B3	T
K0725.6130X12	reamed hole	129	12H7	32	20	51	29	111	20	59	52	53	-	-
K0725.6130X14	reamed hole	129	14H7	32	20	51	29	111	20	59	52	53	-	-
K0725.6160X14	reamed hole	159	14H7	40	25	65	31	126	24	71	55	59	-	-
K0725.6160X16	reamed hole	159	16H7	40	25	65	31	126	24	71	55	59	-	-
K0725.6200X16	reamed hole	200	16H7	54,5	27	80	33	160	28	91	69	69	-	-
K0725.6200X20	reamed hole	200	20H7	54,5	27	80	33	160	28	91	69	69	-	-
K0725.6345X20	reamed hole	346	20H7	67,5	27	148	43,5	144	32	91	80	80	-	-
K0725.7130X12	reamed hole with slot	129	12H7	32	20	51	29	111	20	59	52	53	4	13,8
K0725.7130X14	reamed hole with slot	129	14H7	32	20	51	29	111	20	59	52	53	5	16,3
K0725.7160X14	reamed hole with slot	159	14H7	40	25	65	31	126	24	71	55	59	5	16,3
K0725.7160X16	reamed hole with slot	159	16H7	40	25	65	31	126	24	71	55	59	5	18,3
K0725.7200X16	reamed hole with slot	200	16H7	54,5	27	80	33	160	28	91	69	69	5	18,3
K0725.7200X20	reamed hole with slot	200	20H7	54,5	27	80	33	160	28	91	69	69	6	22,8
K0725.7345X20	reamed hole with slot	346	20H7	67,5	27	148	43,5	144	32	91	80	80	6	22,8