

Wing grips, one-sided with cap

Item description/product images



Description

Material:

Thermoplastic.


Bush steel 5.8 or stainless steel 1.4305.

Version:

Grip black grey.

Bush trivalent blue passivated steel or bright stainless steel.

Drawings



Overview of items

Order No.	Form	Component material	Colour Cap	A	B	D	D2	H	H1	H2	T
K0608.904	K	steel	black grey RAL 7021	22	4,4	M4	12	18	4,5	15,5	10
K0608.9045	K	steel	light grey RAL 7035	22	4,4	M4	12	18	4,5	15,5	10
K0608.9046	K	steel	traffic red RAL 3020	22	4,4	M4	12	18	4,5	15,5	10
K0608.9047	K	steel	colza yellow RAL 1021	22	4,4	M4	12	18	4,5	15,5	10
K0608.905	K	steel	black grey RAL 7021	22	4,4	M5	12	18	4,5	15,5	10
K0608.9055	K	steel	light grey RAL 7035	22	4,4	M5	12	18	4,5	15,5	10
K0608.9056	K	steel	traffic red RAL 3020	22	4,4	M5	12	18	4,5	15,5	10
K0608.9057	K	steel	colza yellow RAL 1021	22	4,4	M5	12	18	4,5	15,5	10
K0608.906	K	steel	black grey RAL 7021	22	4,4	M6	12	18	4,5	15,5	10
K0608.9065	K	steel	light grey RAL 7035	22	4,4	M6	12	18	4,5	15,5	10
K0608.9066	K	steel	traffic red RAL 3020	22	4,4	M6	12	18	4,5	15,5	10
K0608.9067	K	steel	colza yellow RAL 1021	22	4,4	M6	12	18	4,5	15,5	10
K0608.105	K	steel	black grey RAL 7021	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.1055	K	steel	light grey RAL 7035	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.1056	K	steel	traffic red RAL 3020	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.1057	K	steel	colza yellow RAL 1021	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.106	K	steel	black grey RAL 7021	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.1065	K	steel	light grey RAL 7035	27,5	5,1	M6	14	24	5,8	20,8	10

Wing grips, one-sided with cap

Overview of items

Order No.	Form	Component material	Colour Cap	A	B	D	D2	H	H1	H2	T
K0608.1066	K	steel	traffic red RAL 3020	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.1067	K	steel	colza yellow RAL 1021	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.208	K	steel	black grey RAL 7021	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.2085	K	steel	light grey RAL 7035	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.2086	K	steel	traffic red RAL 3020	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.2087	K	steel	colza yellow RAL 1021	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.210	K	steel	black grey RAL 7021	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.2105	K	steel	light grey RAL 7035	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.2106	K	steel	traffic red RAL 3020	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.2107	K	steel	colza yellow RAL 1021	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.0904	K	stainless steel	black grey RAL 7021	22	4,4	M4	12	18	4,5	15,5	10
K0608.09045	K	stainless steel	light grey RAL 7035	22	4,4	M4	12	18	4,5	15,5	10
K0608.09046	K	stainless steel	traffic red RAL 3020	22	4,4	M4	12	18	4,5	15,5	10
K0608.09047	K	stainless steel	colza yellow RAL 1021	22	4,4	M4	12	18	4,5	15,5	10
K0608.0905	K	stainless steel	black grey RAL 7021	22	4,4	M5	12	18	4,5	15,5	10
K0608.09055	K	stainless steel	light grey RAL 7035	22	4,4	M5	12	18	4,5	15,5	10
K0608.09056	K	stainless steel	traffic red RAL 3020	22	4,4	M5	12	18	4,5	15,5	10
K0608.09057	K	stainless steel	colza yellow RAL 1021	22	4,4	M5	12	18	4,5	15,5	10
K0608.0906	K	stainless steel	black grey RAL 7021	22	4,4	M6	12	18	4,5	15,5	10
K0608.09065	K	stainless steel	light grey RAL 7035	22	4,4	M6	12	18	4,5	15,5	10
K0608.09066	K	stainless steel	traffic red RAL 3020	22	4,4	M6	12	18	4,5	15,5	10
K0608.09067	K	stainless steel	colza yellow RAL 1021	22	4,4	M6	12	18	4,5	15,5	10
K0608.0105	K	stainless steel	black grey RAL 7021	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.01055	K	stainless steel	light grey RAL 7035	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.01056	K	stainless steel	traffic red RAL 3020	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.01057	K	stainless steel	colza yellow RAL 1021	27,5	5,1	M5	14	24	5,8	20,8	10
K0608.0106	K	stainless steel	black grey RAL 7021	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.01065	K	stainless steel	light grey RAL 7035	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.01066	K	stainless steel	traffic red RAL 3020	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.01067	K	stainless steel	colza yellow RAL 1021	27,5	5,1	M6	14	24	5,8	20,8	10
K0608.0208	K	stainless steel	black grey RAL 7021	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.02085	K	stainless steel	light grey RAL 7035	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.02086	K	stainless steel	traffic red RAL 3020	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.02087	K	stainless steel	colza yellow RAL 1021	37,5	6,3	M8	21	36	8,5	30,5	14
K0608.0210	K	stainless steel	black grey RAL 7021	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.02105	K	stainless steel	light grey RAL 7035	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.02106	K	stainless steel	traffic red RAL 3020	37,5	6,3	M10	21	36	8,5	30,5	14
K0608.02107	K	stainless steel	colza yellow RAL 1021	37,5	6,3	M10	21	36	8,5	30,5	14