

## Tension levers stainless steel

### Item description/product images



### Description

#### Material:

Steel parts stainless steel 1.4305.

Ball knob black plastic.

#### Version:

Stainless steel parts bright.

Ball knob polished.

#### Note:

Tension levers can be used for simple clamping or control operations.

Where applicable, there must be enough space available so that the grip can be rotated 360°.

#### On request:

Other female threads, reamed holes and special versions.

Dimension "A" available in other lengths at extra charge.

### Overview of items

#### Tension levers stainless steel

Order No.	Thread type	Form	Size	X	T	D	D1	D2	H	H1	H2	A	A2
K1444.2082	internal thread	0°	1	M8	18	24	10	25	40	-	32,5	88,1	-
K1444.2102	internal thread	0°	1	M10	18	24	10	25	40	-	32,5	88,1	-
K1444.21012	internal thread	0°	2	M10	20	28	12	32	46	-	36,5	104	-
K1444.2122	internal thread	0°	2	M12	20	28	12	32	46	-	36,5	104	-
K1444.2162	internal thread	0°	3	M16	23	33	13	32	52	-	41	126,5	-
K1444.2202	internal thread	0°	4	M20	26	41	13	32	61	-	49	128,5	-
K1444.1102	reamed hole	0°	1	10	22	24	10	25	40	-	32,5	88,1	-
K1444.1122	reamed hole	0°	2	12	25	28	12	32	46	-	36,5	104	-
K1444.1142	reamed hole	0°	2	14	25	28	12	32	46	-	36,5	104	-
K1444.1162	reamed hole	0°	3	16	28	33	13	32	52	-	41	126,5	-
K1444.1202	reamed hole	0°	4	20	32	41	13	32	61	-	49	128,5	-
K1444.208	internal thread	20°	1	M8	18	24	10	25	40	52,5	32,5	84,5	15
K1444.210	internal thread	20°	1	M10	18	24	10	25	40	52,5	32,5	84,5	15
K1444.2101	internal thread	20°	2	M10	20	28	12	32	46	61	36,5	100	15
K1444.212	internal thread	20°	2	M12	20	28	12	32	46	61	36,5	100	15
K1444.216	internal thread	20°	3	M16	23	33	13	32	52	72	41	121	15
K1444.220	internal thread	20°	4	M20	26	41	13	32	61	80	49	123	15
K1444.110	reamed hole	20°	1	10	22	24	10	25	40	52,5	32,5	84,5	15
K1444.112	reamed hole	20°	2	12	25	28	12	32	46	61	36,5	100	15
K1444.114	reamed hole	20°	2	14	25	28	12	32	46	61	36,5	100	15
K1444.116	reamed hole	20°	3	16	28	33	13	32	52	72	41	121	15
K1444.120	reamed hole	20°	4	20	32	41	13	32	61	80	49	123	15