

Momento d'attrito (Nm) in base al diametro del foro (mm)																					
Dimensioni	6	10	11	15	15	16	19	20	24	25	28	30	32	35	38	40	42	45	48	50	55
14	8,6	13,8	14,7	22,7																	
19		41	45	62	68	67	83	90													
24					74	72	90	97	112	120	143										
28							189	188	237	250	280	307	310	353	389						
38								269	337	356	398	436	424	501	533	572	585	644			
42											445	506	470	566	581	647	630	728	836	858	
48														955	999	1092	1091	1230	1381	1334	1540