


Push-pull toggle clamp with mounting bracket

Item description/product images



Description

Material:

Steel or stainless steel.

Version:

Steel electro zinc-plated and passivated.

Bright stainless steel.

Plastic grip oil-resistant

Note:

As the push-pull toggle clamps lock in open and closed handle positions, they can be used to clamp when pushing or pulling.

The fastening nut supplied allows the clamps to be mounted in any desired position.

Attention:

The stainless steel versions come without mounting bracket.


Drawing reference:

1) with mounting bracket

2) without mounting bracket

Push-pull toggle clamp with mounting bracket

Drawings



Overview of items

Push-Pull Clamps with mounting bracket

Order No.	Main material	Version 2	hole arrangement	Opening angle of handle	Hand force FH N	Clamping force F1 N	Retaining force F2 N
K1547.01000	steel	with mounting bracket	1	189°	40	500	1000
K1547.02000	steel	with mounting bracket	2	186°	60	1000	2000
K1547.04000	steel	with mounting bracket	3	181°	100	2000	4000
K1547.11000	stainless steel	without mounting bracket	-	189°	40	500	1000
K1547.12000	stainless steel	without mounting bracket	-	186°	60	1000	2000
K1547.14000	stainless steel	without mounting bracket	-	181°	100	2000	4000

Push-pull toggle clamp with mounting bracket

Overview of items

Order No.	Main material	A1	A2	A3	B	B1	B2	B3	C1	C2	C3	D	D1	H	L	L1	L2	L3	L4	M	M1	R	T	Travel S
K1547.01000	steel	30	13,5	10,5	18	44	-	24	26	-	-	5,2	9,4	94,5	64,3	30	8,7	15,8	21,3	M6	M16x1,5	68,5	4	20,3
K1547.02000	steel	41,3	14,4	19	41,3	69,9	41,3	28,6	33	12,7	33,3	5,6	10,9	123	118,7	41,7	11	25,4	40,7	M8	M20x1,5	90	5	40
K1547.04000	steel	62	21	31,8	45,2	76	45,2	40	37	21	52,8	8,5	15,9	164,5	169,2	86	17	32	69	M10	M27x2	127	5	66,7
K1547.11000	stainless steel	-	-	-	-	-	-	-	-	-	-	-	9,4	78	64,3	34	12,7	15,8	21,3	M6	M16x1,5	68,5	-	20,3
K1547.12000	stainless steel	-	-	-	-	-	-	-	-	-	-	-	10,9	100,9	118,7	46,7	16	25,4	40,7	M8	M20x1,5	90	-	40
K1547.14000	stainless steel	-	-	-	-	-	-	-	-	-	-	-	15,9	143	169,2	91	22	32	69	M10	M27x2	127	-	66,7