


# Ball-end thrust screws without head stainless steel with flattened ball

## Item description/product images



## Description

### Material:

Screw and ball stainless steel.

### Version:


Stainless steel bright.

### Note:

Surfaces which are not flat and parallel can be firmly clamped or supported with a flattened ball, the movable ball can adapt itself up to 9°.

Longer versions have been designed especially to be glued in. This enables mechanical connecting elements with external thread to be made cost-effectively for small and medium-sized series.

## Drawings



## Overview of items

### Ball-end thrust screws without head, stainless steel with flattened ball

Order No.	Form	D	D1	L	Ball-Ø	SW	Load rating max. kN (static load only)
K0384.2046	B	M4	1,4	5,8	2,5	2	3,5
K0384.2048	B	M4	1,4	7,8	2,5	2	3,5
K0384.20410	B	M4	1,4	9,8	2,5	2	3,5
K0384.20412	B	M4	1,4	11,8	2,5	2	3,5
K0384.20416	B	M4	1,4	15,8	2,5	2	3,5
K0384.2058	B	M5	2	7,6	3	2,5	4,5

## Ball-end thrust screws without head stainless steel with flattened ball

### Overview of items

Order No.	Form	D	D1	L	Ball-Ø	SW	Load rating max. kN (static load only)
K0384.20510	B	M5	2	9,6	3	2,5	4,5
K0384.20512	B	M5	2	11,6	3	2,5	4,5
K0384.20516	B	M5	2	15,6	3	2,5	4,5
K0384.20520	B	M5	2	19,6	3	2,5	4,5
K0384.20525	B	M5	2	24,6	3	2,5	4,5
K0384.20610	B	M6	3	10,1	4	3	9
K0384.20612	B	M6	3	12,1	4	3	9
K0384.20616	B	M6	3	16,1	4	3	9
K0384.20620	B	M6	3	20,1	4	3	9
K0384.20625	B	M6	3	25,1	4	3	9
K0384.20650	B	M6	3	50,1	4	3	9
K0384.20660	B	M6	3	60,1	4	3	9
K0384.20680	B	M6	3	80,1	4	3	9
K0384.20810	B	M8	4,1	10,3	5,5	4	10
K0384.20812	B	M8	4,1	12,3	5,5	4	10
K0384.20816	B	M8	4,1	16,3	5,5	4	15
K0384.20820	B	M8	4,1	20,3	5,5	4	15
K0384.20825	B	M8	4,1	25,3	5,5	4	15
K0384.20830	B	M8	4,1	30,3	5,5	4	15
K0384.20850	B	M8	4,1	50,3	5,5	4	15
K0384.20860	B	M8	4,1	60,3	5,5	4	15
K0384.20880	B	M8	4,1	80,3	5,5	4	15
K0384.21012	B	M10	5,6	12,3	7	5	20
K0384.21016	B	M10	5,6	16,3	7	5	20
K0384.21020	B	M10	5,6	20,3	7	5	20
K0384.21025	B	M10	5,6	25,3	7	5	20
K0384.21035	B	M10	5,6	35,3	7	5	20
K0384.21216	B	M12	7	16,2	8,5	6	30
K0384.21220	B	M12	7	20,2	8,5	6	30
K0384.21230	B	M12	7	30,2	8,5	6	30
K0384.21240	B	M12	7	40,2	8,5	6	30
K0384.21620	B	M16	10,7	20	12	8	60
K0384.21625	B	M16	10,7	25	12	8	60
K0384.21635	B	M16	10,7	35	12	8	60
K0384.21650	B	M16	10,7	50	12	8	60