

Clevis joints with snap-in pin DIN 71752

Item description/product images



Description


Material:

Clevis and pins free-cutting steel.
Spring, spring steel.

Version:

Trivalent passivated.

Drawings



Overview of items

Clevis joints with snap-in pin DIN 71752

Order No.	Version	B	G	D1	D2	D3	L1	L2	L3	L5	L6	A
K0731.03508	RH thread	4	8	4	M3,5	8	21	16	6	15	10	8
K0731.0510	RH thread	5	10	5	M5	9	26	20	7,5	19	12	10
K0731.0612	RH thread	6	12	6	M6	10	31	24	9	23	14	12
K0731.0816	RH thread	8	16	8	M8	14	42	32	12	31	19	16
K0731.0832	RH thread	8	32	8	M8	14	58	48	12	47	19	16
K0731.1020	RH thread	10	20	10	M10	18	52	40	15	39	23	20
K0731.10120	RH thread	10	20	10	M10x1,25	18	52	40	15	39	23	20
K0731.1040	RH thread	10	40	10	M10	18	72	60	15	59	23	20
K0731.10140	RH thread	10	40	10	M10x1,25	18	72	60	15	59	23	20
K0731.1224	RH thread	12	24	12	M12	20	62	48	18	47	28	24
K0731.12124	RH thread	12	24	12	M12x1,25	20	62	48	18	47	28	24
K0731.1248	RH thread	12	48	12	M12	20	86	72	18	69	28	24
K0731.12148	RH thread	12	48	12	M12x1,25	20	86	72	18	69	28	24
K0731.1428	RH thread	14	28	14	M14	24	72	56	22,5	52	31	27
K0731.1632	RH thread	16	32	16	M16	26	83	64	24	62	36	32
K0731.16132	RH thread	16	32	16	M16x1,5	26	83	64	24	62	36	32
K0731.05101	LH thread	5	10	5	M5	9	26	20	7,5	19	12	10
K0731.06121	LH thread	6	12	6	M6	10	31	24	9	23	14	12
K0731.08161	LH thread	8	16	8	M8	14	42	32	12	31	19	16
K0731.08321	LH thread	8	32	8	M8	14	58	48	12	47	19	16

Clevis joints with snap-in pin DIN 71752

Overview of items

Order No.	Version	B	G	D1	D2	D3	L1	L2	L3	L5	L6	A
K0731.10201	LH thread	10	20	10	M10	18	52	40	15	39	23	20
K0731.10401	LH thread	10	40	10	M10	18	72	60	15	59	23	20
K0731.12241	LH thread	12	24	12	M12	20	62	48	18	47	28	24
K0731.16321	LH thread	16	32	16	M16	26	83	64	24	62	36	32
K0731.2040	RH thread	20	40	20	M20	34	105	80	30	71,5	45	40
K0731.20401	LH thread	20	40	20	M20	34	105	80	30	71,5	45	40