


Cam-action indexing plungers with stop

Item description/product images



black grey RAL 7021	pure orange RAL 2004	colza yellow RAL 1021	traffic red RAL 3020
signal green RAL 6032	traffic blue RAL 5017	light grey RAL 7035	



Description

Product description:

Cam-action indexing plunger are used where any change in locking position due to lateral forces should be prevented. Turning the grip through 180° retracts the indexing pin, enabling a change in the indexed position. The notch ensures that the grip remains in this position and the indexing pin remains retracted. A stop at 180° prevents the lever rotating further and the indexing pin from extending again.

The rotation direction is defined by selecting a left or right stop side.

Material:

Grip 1.0503.

Threaded sleeve and indexing pin free-cutting steel.

Spring 1.4310.

Grip cap thermoplastic PA.

Version:

Threaded sleeve and grip black oxidised.

Indexing pin hardened, ground and black oxidised.

Spring bright.

Grip cap in various colours:

- black grey RAL 7021
- pure orange RAL 2004
- colza yellow RAL 1021
- traffic red RAL 3020
- signal green RAL 6032
- traffic blue RAL 5017
- light grey RAL 7035

Advantages:

Turning the grip through 180° retracts the pin.

Optionally available with coloured plastic grip caps.

180° stop with rotation in one direction.

On request:

Special versions.

Accessory:

Mounting bracket K0638.

Positioning bushes K1290, K1839, K1840.

Drawing reference:

Form A: without grip cap or locknut

Form B: without grip cap, with locknut

Form C: with grip cap, without locknut


Form D: with grip cap and locknut

1) Stop left

2) Stop right

Cam-action indexing plungers with stop

Drawings



Overview of items

Cam action indexing plunger with stop

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.1040410	A	left	-	4	M10	10	38,5	25	15	9	3	6	10	-	1	8	14
K1674.1040510	A	left	-	5	M10	10	38,5	25	15	9	3	6	10	-	1,3	8	14
K1674.1040610	A	left	-	6	M10	10	38,5	25	15	9	3	6	10	-	1,8	8	14
K1674.1040512	A	left	-	5	M12	12	47,4	30	19	10,8	3,6	8	12	-	1,3	5	15
K1674.1040612	A	left	-	6	M12	12	47,4	30	19	10,8	3,6	8	12	-	1,8	5	15
K1674.1040812	A	left	-	8	M12	12	47,4	30	19	10,8	3,6	8	12	-	2,3	5	15
K1674.1040616	A	left	-	6	M16	16	61,2	40	26	14,4	4,8	10	16	-	1,8	15	35
K1674.1040816	A	left	-	8	M16	16	61,2	40	26	14,4	4,8	10	16	-	2,3	15	35
K1674.1041016	A	left	-	10	M16	16	61,2	40	26	14,4	4,8	10	16	-	2,8	15	35
K1674.10408201	A	left	-	8	M20x1,5	20	71	50	30	18	6	12	20	-	2,3	20	60
K1674.10410201	A	left	-	10	M20x1,5	20	71	50	30	18	6	12	20	-	2,8	20	60
K1674.10412201	A	left	-	12	M20x1,5	20	71	50	30	18	6	12	20	-	3	20	60
K1674.2040410	A	right	-	4	M10	10	38,5	25	15	9	3	6	10	-	1	8	14
K1674.2040510	A	right	-	5	M10	10	38,5	25	15	9	3	6	10	-	1,3	8	14
K1674.2040610	A	right	-	6	M10	10	38,5	25	15	9	3	6	10	-	1,8	8	14
K1674.2040512	A	right	-	5	M12	12	47,4	30	19	10,8	3,6	8	12	-	1,3	5	15
K1674.2040612	A	right	-	6	M12	12	47,4	30	19	10,8	3,6	8	12	-	1,8	5	15
K1674.2040812	A	right	-	8	M12	12	47,4	30	19	10,8	3,6	8	12	-	2,3	5	15
K1674.2040616	A	right	-	6	M16	16	61,2	40	26	14,4	4,8	10	16	-	1,8	15	35
K1674.2040816	A	right	-	8	M16	16	61,2	40	26	14,4	4,8	10	16	-	2,3	15	35
K1674.2041016	A	right	-	10	M16	16	61,2	40	26	14,4	4,8	10	16	-	2,8	15	35
K1674.20408201	A	right	-	8	M20x1,5	20	71	50	30	18	6	12	20	-	2,3	20	60
K1674.20410201	A	right	-	10	M20x1,5	20	71	50	30	18	6	12	20	-	2,8	20	60
K1674.20412201	A	right	-	12	M20x1,5	20	71	50	30	18	6	12	20	-	3	20	60
K1674.1050410	B	left	-	4	M10	10	38,5	25	15	9	3	6	10	17	1	8	14
K1674.1050510	B	left	-	5	M10	10	38,5	25	15	9	3	6	10	17	1,3	8	14
K1674.1050610	B	left	-	6	M10	10	38,5	25	15	9	3	6	10	17	1,8	8	14
K1674.1050512	B	left	-	5	M12	12	47,4	30	19	10,8	3,6	8	12	19	1,3	5	15
K1674.1050612	B	left	-	6	M12	12	47,4	30	19	10,8	3,6	8	12	19	1,8	5	15
K1674.1050812	B	left	-	8	M12	12	47,4	30	19	10,8	3,6	8	12	19	2,3	5	15
K1674.1050616	B	left	-	6	M16	16	61,2	40	26	14,4	4,8	10	16	24	1,8	15	35
K1674.1050816	B	left	-	8	M16	16	61,2	40	26	14,4	4,8	10	16	24	2,3	15	35
K1674.1051016	B	left	-	10	M16	16	61,2	40	26	14,4	4,8	10	16	24	2,8	15	35
K1674.10508201	B	left	-	8	M20x1,5	20	71	50	30	18	6	12	20	30	2,3	20	60

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.10510201	B	left	-	10	M20x1,5	20	71	50	30	18	6	12	20	30	2,8	20	60
K1674.10512201	B	left	-	12	M20x1,5	20	71	50	30	18	6	12	20	30	3	20	60
K1674.2050410	B	right	-	4	M10	10	38,5	25	15	9	3	6	10	17	1	8	14
K1674.2050510	B	right	-	5	M10	10	38,5	25	15	9	3	6	10	17	1,3	8	14
K1674.2050610	B	right	-	6	M10	10	38,5	25	15	9	3	6	10	17	1,8	8	14
K1674.2050512	B	right	-	5	M12	12	47,4	30	19	10,8	3,6	8	12	19	1,3	5	15
K1674.2050612	B	right	-	6	M12	12	47,4	30	19	10,8	3,6	8	12	19	1,8	5	15
K1674.2050812	B	right	-	8	M12	12	47,4	30	19	10,8	3,6	8	12	19	2,3	5	15
K1674.2050616	B	right	-	6	M16	16	61,2	40	26	14,4	4,8	10	16	24	1,8	15	35
K1674.2050816	B	right	-	8	M16	16	61,2	40	26	14,4	4,8	10	16	24	2,3	15	35
K1674.2051016	B	right	-	10	M16	16	61,2	40	26	14,4	4,8	10	16	24	2,8	15	35
K1674.20508201	B	right	-	8	M20x1,5	20	71	50	30	18	6	12	20	30	2,3	20	60
K1674.20510201	B	right	-	10	M20x1,5	20	71	50	30	18	6	12	20	30	2,8	20	60
K1674.20512201	B	right	-	12	M20x1,5	20	71	50	30	18	6	12	20	30	3	20	60
K1674.1060410	C	left	black grey RAL 7021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.1060510	C	left	black grey RAL 7021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.1060610	C	left	black grey RAL 7021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.1060512	C	left	black grey RAL 7021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.1060612	C	left	black grey RAL 7021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.1060812	C	left	black grey RAL 7021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.1060616	C	left	black grey RAL 7021	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.1060816	C	left	black grey RAL 7021	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.1061016	C	left	black grey RAL 7021	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.10608201	C	left	black grey RAL 7021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.10610201	C	left	black grey RAL 7021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.10612201	C	left	black grey RAL 7021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.10604102	C	left	orange RAL 2004	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.10605102	C	left	orange RAL 2004	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.10606102	C	left	orange RAL 2004	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.10605122	C	left	orange RAL 2004	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.10606122	C	left	orange RAL 2004	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.10608122	C	left	orange RAL 2004	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.10606162	C	left	orange RAL 2004	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.10608162	C	left	orange RAL 2004	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.10610162	C	left	orange RAL 2004	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.106082012	C	left	orange RAL 2004	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.106102012	C	left	orange RAL 2004	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.106122012	C	left	orange RAL 2004	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.106041016	C	left	colza yellow RAL 1021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.106051016	C	left	colza yellow RAL 1021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.106061016	C	left	colza yellow RAL 1021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.106051216	C	left	colza yellow RAL 1021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.106061216	C	left	colza yellow RAL 1021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.106081216	C	left	colza yellow RAL 1021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.106061616	C	left	colza yellow RAL 1021	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.106081616	C	left	colza yellow RAL 1021	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.106101616	C	left	colza yellow RAL 1021	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.1060820116	C	left	colza yellow RAL 1021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.1061020116	C	left	colza yellow RAL 1021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.1061220116	C	left	colza yellow RAL 1021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.106041084	C	left	traffic red RAL 3020	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.106051084	C	left	traffic red RAL 3020	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.106061084	C	left	traffic red RAL 3020	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.106051284	C	left	traffic red RAL 3020	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.106061284	C	left	traffic red RAL 3020	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.106081284	C	left	traffic red RAL 3020	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.106061684	C	left	traffic red RAL 3020	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.106081684	C	left	traffic red RAL 3020	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.106101684	C	left	traffic red RAL 3020	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.1060820184	C	left	traffic red RAL 3020	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.1061020184	C	left	traffic red RAL 3020	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.1061220184	C	left	traffic red RAL 3020	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.106041086	C	left	signal green RAL 6032	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.106051086	C	left	signal green RAL 6032	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.106061086	C	left	signal green RAL 6032	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.106051286	C	left	signal green RAL 6032	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.106061286	C	left	signal green RAL 6032	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.106081286	C	left	signal green RAL 6032	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.106061686	C	left	signal green RAL 6032	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.106081686	C	left	signal green RAL 6032	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.106101686	C	left	signal green RAL 6032	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.1060820186	C	left	signal green RAL 6032	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.1061020186	C	left	signal green RAL 6032	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.1061220186	C	left	signal green RAL 6032	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.106041087	C	left	traffic blue RAL 5017	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.106051087	C	left	traffic blue RAL 5017	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.106061087	C	left	traffic blue RAL 5017	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.106051287	C	left	traffic blue RAL 5017	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.106061287	C	left	traffic blue RAL 5017	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.106081287	C	left	traffic blue RAL 5017	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.106061687	C	left	traffic blue RAL 5017	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.106081687	C	left	traffic blue RAL 5017	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.106101687	C	left	traffic blue RAL 5017	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.1060820187	C	left	traffic blue RAL 5017	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.1061020187	C	left	traffic blue RAL 5017	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.1061220187	C	left	traffic blue RAL 5017	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.106041088	C	left	light grey RAL 7035	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.106051088	C	left	light grey RAL 7035	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.106061088	C	left	light grey RAL 7035	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.106051288	C	left	light grey RAL 7035	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.106061288	C	left	light grey RAL 7035	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.106081288	C	left	light grey RAL 7035	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.106061688	C	left	light grey RAL 7035	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.106081688	C	left	light grey RAL 7035	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.106101688	C	left	light grey RAL 7035	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.1060820188	C	left	light grey RAL 7035	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.1061020188	C	left	light grey RAL 7035	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.1061220188	C	left	light grey RAL 7035	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.2060410	C	right	black grey RAL 7021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.2060510	C	right	black grey RAL 7021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.2060610	C	right	black grey RAL 7021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.2060512	C	right	black grey RAL 7021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.2060612	C	right	black grey RAL 7021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.2060812	C	right	black grey RAL 7021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.2060616	C	right	black grey RAL 7021	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.2060816	C	right	black grey RAL 7021	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.2061016	C	right	black grey RAL 7021	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.20608201	C	right	black grey RAL 7021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.20610201	C	right	black grey RAL 7021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.20612201	C	right	black grey RAL 7021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.20604102	C	right	orange RAL 2004	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.20605102	C	right	orange RAL 2004	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.20606102	C	right	orange RAL 2004	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.20605122	C	right	orange RAL 2004	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.20606122	C	right	orange RAL 2004	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.20608122	C	right	orange RAL 2004	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.20606162	C	right	orange RAL 2004	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.20608162	C	right	orange RAL 2004	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.20610162	C	right	orange RAL 2004	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.206082012	C	right	orange RAL 2004	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.206102012	C	right	orange RAL 2004	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.206122012	C	right	orange RAL 2004	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.206041016	C	right	colza yellow RAL 1021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.206051016	C	right	colza yellow RAL 1021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.206061016	C	right	colza yellow RAL 1021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.206051216	C	right	colza yellow RAL 1021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.206061216	C	right	colza yellow RAL 1021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.206081216	C	right	colza yellow RAL 1021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.206061616	C	right	colza yellow RAL 1021	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.206081616	C	right	colza yellow RAL 1021	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.206101616	C	right	colza yellow RAL 1021	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.2060820116	C	right	colza yellow RAL 1021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.2061020116	C	right	colza yellow RAL 1021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.2061220116	C	right	colza yellow RAL 1021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.206041084	C	right	traffic red RAL 3020	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.206051084	C	right	traffic red RAL 3020	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.206061084	C	right	traffic red RAL 3020	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.206051284	C	right	traffic red RAL 3020	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.206061284	C	right	traffic red RAL 3020	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.206081284	C	right	traffic red RAL 3020	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.206061684	C	right	traffic red RAL 3020	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.206081684	C	right	traffic red RAL 3020	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.206101684	C	right	traffic red RAL 3020	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.2060820184	C	right	traffic red RAL 3020	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.2061020184	C	right	traffic red RAL 3020	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.2061220184	C	right	traffic red RAL 3020	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.206041086	C	right	signal green RAL 6032	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.206051086	C	right	signal green RAL 6032	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.206061086	C	right	signal green RAL 6032	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.206051286	C	right	signal green RAL 6032	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.206061286	C	right	signal green RAL 6032	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.206081286	C	right	signal green RAL 6032	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.206061686	C	right	signal green RAL 6032	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.206081686	C	right	signal green RAL 6032	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.206101686	C	right	signal green RAL 6032	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.2060820186	C	right	signal green RAL 6032	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.2061020186	C	right	signal green RAL 6032	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.2061220186	C	right	signal green RAL 6032	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.206041087	C	right	traffic blue RAL 5017	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.206051087	C	right	traffic blue RAL 5017	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.206061087	C	right	traffic blue RAL 5017	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.206051287	C	right	traffic blue RAL 5017	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.206061287	C	right	traffic blue RAL 5017	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.206081287	C	right	traffic blue RAL 5017	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.206061687	C	right	traffic blue RAL 5017	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.206081687	C	right	traffic blue RAL 5017	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.206101687	C	right	traffic blue RAL 5017	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.2060820187	C	right	traffic blue RAL 5017	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.2061020187	C	right	traffic blue RAL 5017	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.2061220187	C	right	traffic blue RAL 5017	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.206041088	C	right	light grey RAL 7035	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1	8	14
K1674.206051088	C	right	light grey RAL 7035	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,3	8	14
K1674.206061088	C	right	light grey RAL 7035	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	-	1,8	8	14
K1674.206051288	C	right	light grey RAL 7035	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,3	5	15
K1674.206061288	C	right	light grey RAL 7035	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	1,8	5	15
K1674.206081288	C	right	light grey RAL 7035	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	-	2,3	5	15
K1674.206061688	C	right	light grey RAL 7035	6	M16	16	62,8	41,5	26	16,6	7	10	16	-	1,8	15	35
K1674.206081688	C	right	light grey RAL 7035	8	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,3	15	35
K1674.206101688	C	right	light grey RAL 7035	10	M16	16	62,8	41,5	26	16,6	7	10	16	-	2,8	15	35
K1674.2060820188	C	right	light grey RAL 7035	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,3	20	60
K1674.2061020188	C	right	light grey RAL 7035	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	2,8	20	60
K1674.2061220188	C	right	light grey RAL 7035	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	-	3	20	60
K1674.1070410	D	left	black grey RAL 7021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.1070510	D	left	black grey RAL 7021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.1070610	D	left	black grey RAL 7021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.1070512	D	left	black grey RAL 7021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.1070612	D	left	black grey RAL 7021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.1070812	D	left	black grey RAL 7021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.1070616	D	left	black grey RAL 7021	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.1070816	D	left	black grey RAL 7021	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.1071016	D	left	black grey RAL 7021	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.10708201	D	left	black grey RAL 7021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.10710201	D	left	black grey RAL 7021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.10712201	D	left	black grey RAL 7021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.10704102	D	left	orange RAL 2004	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.10705102	D	left	orange RAL 2004	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.10706102	D	left	orange RAL 2004	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.10705122	D	left	orange RAL 2004	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.10706122	D	left	orange RAL 2004	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.10708122	D	left	orange RAL 2004	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.10706162	D	left	orange RAL 2004	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.10708162	D	left	orange RAL 2004	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.10710162	D	left	orange RAL 2004	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.107082012	D	left	orange RAL 2004	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.107102012	D	left	orange RAL 2004	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.107122012	D	left	orange RAL 2004	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.107041016	D	left	colza yellow RAL 1021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.107051016	D	left	colza yellow RAL 1021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.107061016	D	left	colza yellow RAL 1021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.107051216	D	left	colza yellow RAL 1021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.107061216	D	left	colza yellow RAL 1021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.107081216	D	left	colza yellow RAL 1021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.107061616	D	left	colza yellow RAL 1021	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.107081616	D	left	colza yellow RAL 1021	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.107101616	D	left	colza yellow RAL 1021	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.1070820116	D	left	colza yellow RAL 1021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.1071020116	D	left	colza yellow RAL 1021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.1071220116	D	left	colza yellow RAL 1021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.107041084	D	left	traffic red RAL 3020	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.107051084	D	left	traffic red RAL 3020	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.107061084	D	left	traffic red RAL 3020	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.107051284	D	left	traffic red RAL 3020	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.107061284	D	left	traffic red RAL 3020	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.107081284	D	left	traffic red RAL 3020	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.107061684	D	left	traffic red RAL 3020	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.107081684	D	left	traffic red RAL 3020	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.107101684	D	left	traffic red RAL 3020	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.1070820184	D	left	traffic red RAL 3020	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.1071020184	D	left	traffic red RAL 3020	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.1071220184	D	left	traffic red RAL 3020	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.107041086	D	left	signal green RAL 6032	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.107051086	D	left	signal green RAL 6032	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.107061086	D	left	signal green RAL 6032	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.107051286	D	left	signal green RAL 6032	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.107061286	D	left	signal green RAL 6032	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.107081286	D	left	signal green RAL 6032	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.107061686	D	left	signal green RAL 6032	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.107081686	D	left	signal green RAL 6032	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.107101686	D	left	signal green RAL 6032	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.1070820186	D	left	signal green RAL 6032	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.1071020186	D	left	signal green RAL 6032	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.1071220186	D	left	signal green RAL 6032	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.107041087	D	left	traffic blue RAL 5017	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.107051087	D	left	traffic blue RAL 5017	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.107061087	D	left	traffic blue RAL 5017	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.107051287	D	left	traffic blue RAL 5017	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.107061287	D	left	traffic blue RAL 5017	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.107081287	D	left	traffic blue RAL 5017	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.107061687	D	left	traffic blue RAL 5017	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.107081687	D	left	traffic blue RAL 5017	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.107101687	D	left	traffic blue RAL 5017	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.1070820187	D	left	traffic blue RAL 5017	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.1071020187	D	left	traffic blue RAL 5017	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.1071220187	D	left	traffic blue RAL 5017	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.107041088	D	left	light grey RAL 7035	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.107051088	D	left	light grey RAL 7035	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.107061088	D	left	light grey RAL 7035	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.107051288	D	left	light grey RAL 7035	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.107061288	D	left	light grey RAL 7035	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.107081288	D	left	light grey RAL 7035	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.107061688	D	left	light grey RAL 7035	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.107081688	D	left	light grey RAL 7035	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.107101688	D	left	light grey RAL 7035	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.1070820188	D	left	light grey RAL 7035	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.1071020188	D	left	light grey RAL 7035	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.1071220188	D	left	light grey RAL 7035	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.2070410	D	right	black grey RAL 7021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.2070510	D	right	black grey RAL 7021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.2070610	D	right	black grey RAL 7021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.2070512	D	right	black grey RAL 7021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.2070612	D	right	black grey RAL 7021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.2070812	D	right	black grey RAL 7021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.2070616	D	right	black grey RAL 7021	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.2070816	D	right	black grey RAL 7021	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.2071016	D	right	black grey RAL 7021	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.20708201	D	right	black grey RAL 7021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.20710201	D	right	black grey RAL 7021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.20712201	D	right	black grey RAL 7021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.20704102	D	right	orange RAL 2004	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.20705102	D	right	orange RAL 2004	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.20706102	D	right	orange RAL 2004	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.20705122	D	right	orange RAL 2004	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.20706122	D	right	orange RAL 2004	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.20708122	D	right	orange RAL 2004	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.20706162	D	right	orange RAL 2004	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.20708162	D	right	orange RAL 2004	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.20710162	D	right	orange RAL 2004	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.207082012	D	right	orange RAL 2004	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.207102012	D	right	orange RAL 2004	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.207122012	D	right	orange RAL 2004	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.207041016	D	right	colza yellow RAL 1021	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.207051016	D	right	colza yellow RAL 1021	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.207061016	D	right	colza yellow RAL 1021	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.207051216	D	right	colza yellow RAL 1021	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.207061216	D	right	colza yellow RAL 1021	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.207081216	D	right	colza yellow RAL 1021	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.207061616	D	right	colza yellow RAL 1021	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.207081616	D	right	colza yellow RAL 1021	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.207101616	D	right	colza yellow RAL 1021	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.2070820116	D	right	colza yellow RAL 1021	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.2071020116	D	right	colza yellow RAL 1021	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.2071220116	D	right	colza yellow RAL 1021	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.207041084	D	right	traffic red RAL 3020	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.207051084	D	right	traffic red RAL 3020	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.207061084	D	right	traffic red RAL 3020	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14

Cam-action indexing plungers with stop

Overview of items

Order No.	Form	Version 2	Component colour	D	D1	D2	L	L1	L3	B	B1	H	SW1	SW2	Fx30°	Spring force initial pressure F1 approx. N	Spring force final pressure F2 approx. N
K1674.207051284	D	right	traffic red RAL 3020	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.207061284	D	right	traffic red RAL 3020	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.207081284	D	right	traffic red RAL 3020	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.207061684	D	right	traffic red RAL 3020	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.207081684	D	right	traffic red RAL 3020	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.207101684	D	right	traffic red RAL 3020	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.2070820184	D	right	traffic red RAL 3020	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.2071020184	D	right	traffic red RAL 3020	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.2071220184	D	right	traffic red RAL 3020	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.207041086	D	right	signal green RAL 6032	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.207051086	D	right	signal green RAL 6032	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.207061086	D	right	signal green RAL 6032	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.207051286	D	right	signal green RAL 6032	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.207061286	D	right	signal green RAL 6032	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.207081286	D	right	signal green RAL 6032	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.207061686	D	right	signal green RAL 6032	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.207081686	D	right	signal green RAL 6032	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.207101686	D	right	signal green RAL 6032	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.2070820186	D	right	signal green RAL 6032	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.2071020186	D	right	signal green RAL 6032	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.2071220186	D	right	signal green RAL 6032	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.207041087	D	right	traffic blue RAL 5017	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.207051087	D	right	traffic blue RAL 5017	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.207061087	D	right	traffic blue RAL 5017	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.207051287	D	right	traffic blue RAL 5017	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.207061287	D	right	traffic blue RAL 5017	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.207081287	D	right	traffic blue RAL 5017	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.207061687	D	right	traffic blue RAL 5017	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.207081687	D	right	traffic blue RAL 5017	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.207101687	D	right	traffic blue RAL 5017	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.2070820187	D	right	traffic blue RAL 5017	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.2071020187	D	right	traffic blue RAL 5017	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.2071220187	D	right	traffic blue RAL 5017	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60
K1674.207041088	D	right	light grey RAL 7035	4	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1	8	14
K1674.207051088	D	right	light grey RAL 7035	5	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,3	8	14
K1674.207061088	D	right	light grey RAL 7035	6	M10	10	39,5	26,3	15	10,9	4,9	6	10	17	1,8	8	14
K1674.207051288	D	right	light grey RAL 7035	5	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,3	5	15
K1674.207061288	D	right	light grey RAL 7035	6	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	1,8	5	15
K1674.207081288	D	right	light grey RAL 7035	8	M12	12	48,4	31,1	19	12,9	5,7	8	12	19	2,3	5	15
K1674.207061688	D	right	light grey RAL 7035	6	M16	16	62,8	41,5	26	16,6	7	10	16	24	1,8	15	35
K1674.207081688	D	right	light grey RAL 7035	8	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,3	15	35
K1674.207101688	D	right	light grey RAL 7035	10	M16	16	62,8	41,5	26	16,6	7	10	16	24	2,8	15	35
K1674.2070820188	D	right	light grey RAL 7035	8	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,3	20	60
K1674.2071020188	D	right	light grey RAL 7035	10	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	2,8	20	60
K1674.2071220188	D	right	light grey RAL 7035	12	M20x1,5	20	72,3	51,3	30	20,5	8,5	12	20	30	3	20	60