

Star grips similar to DIN 6336, metal parts stainless steel, internal thread, with cap, Form K

Item description/product images



Description

Material:

Black thermoplastic, bush in stainless steel 1.4305.


Version:

Bush bright.

On request:

Other colours or designs, such as company logo.

Drawings



Overview of items

Order No.	Colour Cap	Form	D	D1	D8	H	H3	T
K0154.204	black grey RAL 7021	K	M4	25	12	16	8	10
K0154.2045	light grey RAL 7035	K	M4	25	12	16	8	10
K0154.2046	traffic red RAL 3020	K	M4	25	12	16	8	10
K0154.2047	colza yellow RAL 1021	K	M4	25	12	16	8	10
K0154.205	black grey RAL 7021	K	M5	25	12	16	8	10
K0154.2055	light grey RAL 7035	K	M5	25	12	16	8	10
K0154.2056	traffic red RAL 3020	K	M5	25	12	16	8	10
K0154.2057	colza yellow RAL 1021	K	M5	25	12	16	8	10
K0154.2061	black grey RAL 7021	K	M6	25	12	16	8	10
K0154.20615	light grey RAL 7035	K	M6	25	12	16	8	10
K0154.20616	traffic red RAL 3020	K	M6	25	12	16	8	10
K0154.20617	colza yellow RAL 1021	K	M6	25	12	16	8	10
K0154.2051	black grey RAL 7021	K	M5	32	14	20	10	10
K0154.20515	light grey RAL 7035	K	M5	32	14	20	10	10
K0154.20516	traffic red RAL 3020	K	M5	32	14	20	10	10
K0154.20517	colza yellow RAL 1021	K	M5	32	14	20	10	10
K0154.206	black grey RAL 7021	K	M6	32	14	20	10	10
K0154.2065	light grey RAL 7035	K	M6	32	14	20	10	10
K0154.2066	traffic red RAL 3020	K	M6	32	14	20	10	10

Star grips similar to DIN 6336, metal parts stainless steel, internal thread, with cap, Form K

Overview of items

Order No.	Colour Cap	Form	D	D1	D8	H	H3	T
K0154.2067	colza yellow RAL 1021	K	M6	32	14	20	10	10
K0154.208	black grey RAL 7021	K	M8	40	18	25	13	14
K0154.2085	light grey RAL 7035	K	M8	40	18	25	13	14
K0154.2086	traffic red RAL 3020	K	M8	40	18	25	13	14
K0154.2087	colza yellow RAL 1021	K	M8	40	18	25	13	14
K0154.2101	black grey RAL 7021	K	M10	40	18	25	13	14
K0154.21015	light grey RAL 7035	K	M10	40	18	25	13	14
K0154.21016	traffic red RAL 3020	K	M10	40	18	25	13	14
K0154.21017	colza yellow RAL 1021	K	M10	40	18	25	13	14
K0154.2081	black grey RAL 7021	K	M8	50	22	32	17	14
K0154.20815	light grey RAL 7035	K	M8	50	22	32	17	14
K0154.20816	traffic red RAL 3020	K	M8	50	22	32	17	14
K0154.20817	colza yellow RAL 1021	K	M8	50	22	32	17	14
K0154.210	black grey RAL 7021	K	M10	50	22	32	17	14
K0154.2105	light grey RAL 7035	K	M10	50	22	32	17	14
K0154.2106	traffic red RAL 3020	K	M10	50	22	32	17	14
K0154.2107	colza yellow RAL 1021	K	M10	50	22	32	17	14
K0154.2121	black grey RAL 7021	K	M12	50	22	32	17	18
K0154.21215	light grey RAL 7035	K	M12	50	22	32	17	18
K0154.21216	traffic red RAL 3020	K	M12	50	22	32	17	18
K0154.21217	colza yellow RAL 1021	K	M12	50	22	32	17	18
K0154.2102	black grey RAL 7021	K	M10	63	26	40	21	14
K0154.21025	light grey RAL 7035	K	M10	63	26	40	21	14
K0154.21026	traffic red RAL 3020	K	M10	63	26	40	21	14
K0154.21027	colza yellow RAL 1021	K	M10	63	26	40	21	14
K0154.212	black grey RAL 7021	K	M12	63	26	40	21	18
K0154.2125	light grey RAL 7035	K	M12	63	26	40	21	18
K0154.2126	traffic red RAL 3020	K	M12	63	26	40	21	18
K0154.2127	colza yellow RAL 1021	K	M12	63	26	40	21	18
K0154.216	black grey RAL 7021	K	M16	63	26	40	21	18
K0154.2165	light grey RAL 7035	K	M16	63	26	40	21	18
K0154.2166	traffic red RAL 3020	K	M16	63	26	40	21	18
K0154.2167	colza yellow RAL 1021	K	M16	63	26	40	21	18