Clamp strap assemblies goose-neck

Item description/product images



Description

Material:
QT steel.
Screws tempered grade 8.8

Version:
Straps painted.
Screws black oxidised.

Note:
“F” is dependent on the depth of the DIN 650 slot.

Drawings



Overview of items

Clamp strap assemblies, goose-neck

Order No.	L	A	A1	B	B1	E1	E2	F	G for T-slot	D	D1	M	F kN
K1450.1010	100	15	30	30	15	32	32	22-46	10	M10x80	M10	12	13,9
K1450.1212	125	20	40	40	20	40	40	28-58	12	M12x100	M12	16	20,2
K1450.1214	125	20	40	40	20	40	40	28-56	14	M12x100	M12	16	20,2
K1450.1616	160	25	50	50	25	49	50	36-72	16	M16x125	M16	20	37,8
K1450.1618	160	25	50	50	25	49	50	36-69	18	M16x125	M16	20	37,8
K1450.2020	200	30	60	60	30	55	70	43-92	20	M20x160	M20	24	58,8
K1450.2022	200	30	60	60	30	55	70	43-92	22	M20x160	M20	24	58,8

© HEINRICH KIPP WERK GmbH & Co. KG