# Crank handles aluminium with fold-away grip

## Item description/product images

## Description

**Material:**
Crank aluminium.
Cylinder grip thermoplastic and steel.

**Version:**
Crank black powder-coated.
Thermoplastic black grey.
Steel parts black oxidised.

**Note:**
Similar to DIN 469.
Versions with transverse bore are secured using the ISO 4027 (DIN 914) grub screw.

## Drawings




## Overview of items

### Crank handles aluminium with fold-away cylinder grip

| Order No. | Version 1 | Version 2 | A | D | D2 | D3 | D7 | H | H1 | H2 | H3 | H4 | L | SW |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **K0997.1110** | reamed hole | without transverse hole | 80 | 24 | 10 | 16 | - | 89 | 49 | 22 | 13,4 | - | 100 | - |
| **K0997.1212** | reamed hole | without transverse hole | 100 | 28 | 12 | 20 | - | 108 | 59,5 | 26 | 16 | - | 124 | - |
| **K0997.1314** | reamed hole | without transverse hole | 125 | 30 | 14 | 25 | - | 140 | 83 | 28 | 15,8 | - | 153 | - |
| **K0997.1417** | reamed hole | without transverse hole | 160 | 34 | 17 | 25 | - | 144 | 83 | 32 | 19,6 | - | 190 | - |

© HEINRICH KIPP WERK GmbH & Co. KG

# Crank handles aluminium with fold-away grip

## Overview of items

| Order No. | Version 1 | Version 2 | A | D | D2 | D3 | D7 | H | H1 | H2 | H3 | H4 | L | SW |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **K0997.11106** | reamed hole | fold-down | 80 | 24 | 10 | 16 | M6 | 89 | 49 | 22 | 13,4 | 7,5 | 100 | - |
| **K0997.12126** | reamed hole | fold-down | 100 | 28 | 12 | 20 | M6 | 107,9 | 59,4 | 26 | 16 | 7,5 | 124 | - |
| **K0997.13146** | reamed hole | fold-down | 125 | 30 | 14 | 26 | M6 | 140,5 | 83,5 | 28 | 15,8 | 7,5 | 153 | - |
| **K0997.14176** | reamed hole | fold-down | 160 | 34 | 17 | 26 | M6 | 144,5 | 83,5 | 32 | 19,6 | 7,5 | 190 | - |
| **K0997.2110** | square socket | without transverse hole | 80 | 24 | - | 16 | - | 89 | 49 | 22 | 13,4 | - | 100 | 10 |
| **K0997.2212** | square socket | without transverse hole | 100 | 28 | - | 20 | - | 108 | 59,5 | 26 | 16 | - | 124 | 12 |
| **K0997.2314** | square socket | without transverse hole | 125 | 30 | - | 25 | - | 140 | 83 | 28 | 15,8 | - | 153 | 14 |
| **K0997.2417** | square socket | without transverse hole | 160 | 34 | - | 25 | - | 144 | 83 | 32 | 19,6 | - | 190 | 17 |
| **K0997.21106** | square socket | fold-down | 80 | 24 | - | 16 | M6 | 89 | 49 | 22 | 13,4 | 7,5 | 100 | 10 |
| **K0997.22126** | square socket | fold-down | 100 | 28 | - | 20 | M6 | 107,9 | 59,4 | 26 | 16 | 7,5 | 124 | 12 |
| **K0997.23146** | square socket | fold-down | 125 | 30 | - | 26 | M6 | 140,5 | 83,5 | 28 | 15,8 | 7,5 | 153 | 14 |
| **K0997.24176** | square socket | fold-down | 160 | 34 | - | 26 | M6 | 144,5 | 83,5 | 32 | 19,6 | 7,5 | 190 | 17 |

© HEINRICH KIPP WERK GmbH & Co. KG