


## Security hinge switches

### Item description/product images



### Description

#### Product description:

The security hinge switches are used for monitoring the position of swing-hinged safety doors, protective hatches and hoods. The protective device is monitored directly in the hinge.

By the universally pre-set versions, the switching angle is freely adjustable over the entire working range. A mounting aid ensures the quick alignment to doors and posts.

The additional hinges have the same appearance and dimensions as the security hinge switches.

#### Material:

Housing, die-cast zinc.

Housing cover, plastic, self-extinguishing.

Hinge bolts, die-cast zinc/steel C45.

Contacts, silver-nickel alloy.

#### Note:

The loading values given for the hinges are non-binding reference values without consideration of safety factors and exclude any liability. The values given are for information purposes only and do not constitute a legally binding assurance of properties.

The load values have been determined under laboratory conditions. It must be determined individually whether the hinge is suitable for the respective application.

Different materials onto which the hinges are installed and the type of mounting, weather conditions and wear can influence the determined values.

#### Technical data:

See Downloads, Technical Information.

#### Assembly:

4x DIN 7984 or DIN EN ISO 4762 M6 socket head screws,

Tightening torque 4.3 Nm

General assembly instructions can be found in the accompanying operating instructions.

#### Advantages:

- Suitable for protection on swivel hatches
- Minimum assembly required, especially on conventional aluminium profiles
- Optimum integration into the surrounding structure
- Additional protection against tampering
- Hardly any mechanical wear


#### Accessory:

For Form A:


Connector bush M12x1 with screw lock K1498

## Security hinge switches

### Item description/product images



### Drawings



### Overview of items

#### Security hinge switches

Order No.	Item	Form	A	B	Default setting	Contacts	Connection type	Connection position	F1 N	F2 N
K1499.781161111	Security Hinge Switch	A	78	116	external mounting	1C / 20	Connector	bottom	5000	5000
K1499.781161112	Security Hinge Switch	A	78	116	external mounting	1C / 20	Connector	top	5000	5000
K1499.781162111	Security Hinge Switch	A	78	116	universal	1C / 20	Connector	bottom	5000	5000
K1499.781162112	Security Hinge Switch	A	78	116	universal	1C / 20	Connector	top	5000	5000
K1499.781161121	Security Hinge Switch	B	78	116	external mounting	1C / 20	cable	bottom	5000	5000
K1499.781161122	Security Hinge Switch	B	78	116	external mounting	1C / 20	cable	top	5000	5000
K1499.781162121	Security Hinge Switch	B	78	116	universal	1C / 20	cable	bottom	5000	5000
K1499.781162122	Security Hinge Switch	B	78	116	universal	1C / 20	cable	top	5000	5000
K1499.78116	Additional Hinge	-	78	116	-	-	-	-	5000	5000

