



Handwheel washers

Item description/product images



Description

Material:

Steel.

Stainless steel 1.4305.

Version:

Steel black oxidised.

Stainless steel bright.

Note:

These washers are used together with DIN EN ISO 2009 or DIN EN ISO 10642 countersunk screws on the end of shafts with keyways to secure handwheels and crank handles.

The washers can be used with the handwheels K0671, K0160, K0161, K0162, K0163, K0164, K0165.

The steel washers are often used as caps for magnets.

Drawing reference:

D3 = for countersunk screw ISO 2009 and ISO 10642


1) countersunk screw ISO 2009 and ISO 10642

2) washer

3) handwheel

4) shaft

Drawings



Overview of items

Handwheel washers

Order No.	Main material	D1	D2	D3	H	G
K0173.00310	0.0061	3,2	10	6	2	M3
K0173.00313	0.0061	3,2	13	6	2	M3

Handwheel washers

Overview of items

Order No.	Main material	D1	D2	D3	H	G
K0173.00416	0.0027	4,3	16	8,4	3	M4
K0173.00420	0.0027	4,3	20	8,4	3	M4
K0173.00520	0.01	5,3	20	10	3,5	M5
K0173.00522	0.0027	5,3	22	10	3,5	M5
K0173.00525	0.0027	5,3	25	10	3,5	M5
K0173.00528	0.0027	5,3	28	10	3,5	M5
K0173.00630	0.01	6,4	30	12	4	M6
K0173.00632	0.0027	6,4	32	12	4	M6
K0173.00636	0.0027	6,4	36	12	4	M6
K0173.00640	0.0027	6,4	40	12	5	M6
K0173.00645	0.0027	6,4	45	12	6	M6
K0173.00652	0.0027	6,4	52	12	6	M6
K0173.10310	250 mm / M12x1 / M8	3,2	10	6	2	M3
K0173.10313	250 mm / M12x1 / M8	3,2	13	6	2	M3
K0173.10416	24 V DC	4,3	16	8,4	3	M4
K0173.10420	24 V DC	4,3	20	8,4	3	M4
K0173.10520	2-piece with locking lever, incl. VA disc	5,3	20	10	3,5	M5
K0173.10522	24 V DC	5,3	22	10	3,5	M5
K0173.10525	24 V DC	5,3	25	10	3,5	M5
K0173.10528	24 V DC	5,3	28	10	3,5	M5
K0173.10630	2-piece with locking lever, incl. VA disc	6,4	30	12	4	M6
K0173.10632	24 V DC	6,4	32	12	4	M6
K0173.10636	24 V DC	6,4	36	12	4	M6
K0173.10640	24 V DC	6,4	40	12	5	M6
K0173.10645	24 V DC	6,4	45	12	6	M6
K0173.10652	24 V DC	6,4	52	12	6	M6