


Spherical knobs revolving

Item description/product images




Description

Version:

Trivalent blue passivated steel or bright stainless steel.

Circlips electro zinc-plated, including stainless steel version.

Drawings



Overview of items

Spherical knobs revolving

| Order No. | Component material | Colour Cap | D | D1 | D2 | D3 | D4 | H | H1 | H2 | L | L2 | L3 | L4 | SW |
|------------|--------------------|-----------------------|----|----|------|----|----|----|-----|-----|----|----|----|----|----|
| K0254.106 | steel | black grey RAL 7021 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1061 | steel | orange RAL 2004 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1062 | steel | signal green RAL 6032 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1063 | steel | blue RAL5017 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1065 | steel | light grey RAL 7035 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1066 | steel | traffic red RAL 3020 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.1067 | steel | colza yellow RAL 1021 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.208 | steel | black grey RAL 7021 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.2081 | steel | orange RAL 2004 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.2082 | steel | signal green RAL 6032 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.2083 | steel | blue RAL5017 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.2085 | steel | light grey RAL 7035 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |

Spherical knobs revolving

Overview of items

| Order No. | Component material | Colour Cap | D | D1 | D2 | D3 | D4 | H | H1 | H2 | L | L2 | L3 | L4 | SW |
|-------------|--------------------|-----------------------|-----|----|------|----|----|----|-----|-----|----|----|----|----|----|
| K0254.2086 | steel | traffic red RAL 3020 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.2087 | steel | colza yellow RAL 1021 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.310 | steel | black grey RAL 7021 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3101 | steel | orange RAL 2004 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3102 | steel | signal green RAL 6032 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3103 | steel | blue RAL5017 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3105 | steel | light grey RAL 7035 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3106 | steel | traffic red RAL 3020 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.3107 | steel | colza yellow RAL 1021 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.412 | steel | black grey RAL 7021 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4121 | steel | orange RAL 2004 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4122 | steel | signal green RAL 6032 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4123 | steel | blue RAL5017 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4125 | steel | light grey RAL 7035 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4126 | steel | traffic red RAL 3020 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.4127 | steel | colza yellow RAL 1021 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.0106 | stainless steel | black grey RAL 7021 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01061 | stainless steel | orange RAL 2004 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01062 | stainless steel | signal green RAL 6032 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01063 | stainless steel | blue RAL5017 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01065 | stainless steel | light grey RAL 7035 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01066 | stainless steel | traffic red RAL 3020 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.01067 | stainless steel | colza yellow RAL 1021 | M6 | 25 | 12 | 17 | 8 | 25 | 3 | 2 | 10 | 15 | 5 | 5 | 7 |
| K0254.0208 | stainless steel | black grey RAL 7021 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02081 | stainless steel | orange RAL 2004 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02082 | stainless steel | signal green RAL 6032 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02083 | stainless steel | blue RAL5017 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02085 | stainless steel | light grey RAL 7035 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02086 | stainless steel | traffic red RAL 3020 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.02087 | stainless steel | colza yellow RAL 1021 | M8 | 32 | 15,5 | 19 | 10 | 33 | 3,5 | 2,6 | 12 | 20 | 6 | 6 | 8 |
| K0254.0310 | stainless steel | black grey RAL 7021 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03101 | stainless steel | orange RAL 2004 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03102 | stainless steel | signal green RAL 6032 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03103 | stainless steel | blue RAL5017 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03105 | stainless steel | light grey RAL 7035 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03106 | stainless steel | traffic red RAL 3020 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.03107 | stainless steel | colza yellow RAL 1021 | M10 | 40 | 19 | 23 | 13 | 41 | 4 | 3 | 15 | 25 | 7 | 10 | 10 |
| K0254.0412 | stainless steel | black grey RAL 7021 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04121 | stainless steel | orange RAL 2004 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04122 | stainless steel | signal green RAL 6032 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04123 | stainless steel | blue RAL5017 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04125 | stainless steel | light grey RAL 7035 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04126 | stainless steel | traffic red RAL 3020 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |
| K0254.04127 | stainless steel | colza yellow RAL 1021 | M12 | 50 | 24 | 31 | 16 | 51 | 5,5 | 4,5 | 20 | 30 | 8 | 8 | 13 |