



Knurled knobs, metal parts stainless steel, Form K, with tapped bush, with cap

Item description/product images



Description

Material:


Thermoplastic, black grey.

Bush and screw stainless steel 1.4305.

Version:

Stainless steel bright.

Drawings



Overview of items

Knurled knobs, metal parts stainless steel, Form K, with tapped bush, with cap

| Order No. | Form | Colour Cap | Size | D | D1 | D2 | H | H1 | T |
|-------------|------|-----------------------|------|----|----|------|----|----|----|
| K0261.2105 | K | black grey RAL 7021 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21051 | K | orange RAL 2004 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21052 | K | signal green RAL6032 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21053 | K | blue RAL5017 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21055 | K | light grey RAL 7035 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21056 | K | traffic red RAL 3020 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21057 | K | colza yellow RAL 1021 | 1 | M5 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.2106 | K | black grey RAL 7021 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21061 | K | orange RAL 2004 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21062 | K | signal green RAL6032 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21063 | K | blue RAL5017 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21065 | K | light grey RAL 7035 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |

Knurled knobs, metal parts stainless steel, Form K, with tapped bush, with cap

Overview of items

| Order No. | Form | Colour Cap | Size | D | D1 | D2 | H | H1 | T |
|-------------|------|-----------------------|------|-----|----|------|----|----|----|
| K0261.21066 | K | traffic red RAL 3020 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21067 | K | colza yellow RAL 1021 | 1 | M6 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.2108 | K | black grey RAL 7021 | 1 | M8 | 40 | 16,5 | 31 | 13 | 14 |
| K0261.21081 | K | orange RAL 2004 | 1 | M8 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21082 | K | signal green RAL6032 | 1 | M8 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21083 | K | blue RAL5017 | 1 | M8 | 40 | 16,5 | 31 | 13 | 10 |
| K0261.21085 | K | light grey RAL 7035 | 1 | M8 | 40 | 16,5 | 31 | 13 | 14 |
| K0261.21086 | K | traffic red RAL 3020 | 1 | M8 | 40 | 16,5 | 31 | 13 | 14 |
| K0261.21087 | K | colza yellow RAL 1021 | 1 | M8 | 40 | 16,5 | 31 | 13 | 14 |
| K0261.2208 | K | black grey RAL 7021 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22081 | K | orange RAL 2004 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22082 | K | signal green RAL6032 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22083 | K | blue RAL5017 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22085 | K | light grey RAL 7035 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22086 | K | traffic red RAL 3020 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.22087 | K | colza yellow RAL 1021 | 2 | M8 | 50 | 18 | 36 | 15 | 14 |
| K0261.2210 | K | black grey RAL 7021 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22101 | K | orange RAL 2004 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22102 | K | signal green RAL6032 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22103 | K | blue RAL5017 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22105 | K | light grey RAL 7035 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22106 | K | traffic red RAL 3020 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.22107 | K | colza yellow RAL 1021 | 2 | M10 | 50 | 18 | 36 | 15 | 14 |
| K0261.2310 | K | black grey RAL 7021 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23101 | K | orange RAL 2004 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23102 | K | signal green RAL6032 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23103 | K | blue RAL5017 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23105 | K | light grey RAL 7035 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23106 | K | traffic red RAL 3020 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.23107 | K | colza yellow RAL 1021 | 3 | M10 | 63 | 22 | 41 | 17 | 14 |
| K0261.2312 | K | black grey RAL 7021 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23121 | K | orange RAL 2004 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23122 | K | signal green RAL6032 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23123 | K | blue RAL5017 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23125 | K | light grey RAL 7035 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23126 | K | traffic red RAL 3020 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |
| K0261.23127 | K | colza yellow RAL 1021 | 3 | M12 | 63 | 22 | 41 | 17 | 18 |