

## Tongue steel, with stop

### Item description/product images



### Description


**Material:**  
Steel.

**Version:**  
Electro zinc-plated.

**Note:**  
\*A in mm by housing length H=18 mm, H=30 mm and H=50 mm.

**Accessory:**  
Quarter-turn lock zinc, lockable K2216.  
quarter-turn lock zinc, lockable, long version K2217.

### Drawings



### Overview of items

## Tongue steel, with stop

### Overview of items

#### Tongue steel, with stop

| Order No.   | Version 2        | A<br>for housing length<br>H=18 | A<br>for housing length<br>H=30 | A<br>for housing length<br>H=50 | B  | B1  | L  |
|-------------|------------------|---------------------------------|---------------------------------|---------------------------------|----|-----|----|
| K2218.13506 | offset upwards   | 6                               | 18                              | 38                              | 19 | 8,1 | 35 |
| K2218.13508 | offset upwards   | 8                               | 20                              | 40                              | 19 | 8,1 | 35 |
| K2218.13510 | offset upwards   | 10                              | 22                              | 42                              | 19 | 8,1 | 35 |
| K2218.13513 | offset upwards   | 13                              | 25                              | 45                              | 19 | 8,1 | 35 |
| K2218.13514 | offset upwards   | 14                              | 26                              | 46                              | 19 | 8,1 | 35 |
| K2218.13516 | offset upwards   | 16                              | 28                              | 48                              | 19 | 8,1 | 35 |
| K2218.13518 | straight         | 18                              | 30                              | 50                              | 19 | 8,1 | 35 |
| K2218.13520 | offset downwards | 20                              | 32                              | 52                              | 19 | 8,1 | 35 |
| K2218.13522 | offset downwards | 22                              | 34                              | 54                              | 19 | 8,1 | 35 |
| K2218.13524 | offset downwards | 24                              | 36                              | 56                              | 19 | 8,1 | 35 |
| K2218.13526 | offset downwards | 26                              | 38                              | 58                              | 19 | 8,1 | 35 |
| K2218.13528 | offset downwards | 28                              | 40                              | 60                              | 19 | 8,1 | 35 |
| K2218.14504 | offset upwards   | 4                               | 16                              | 36                              | 19 | 8,1 | 45 |
| K2218.14506 | offset upwards   | 6                               | 18                              | 38                              | 19 | 8,1 | 45 |
| K2218.14508 | offset upwards   | 8                               | 20                              | 40                              | 19 | 8,1 | 45 |
| K2218.14510 | offset upwards   | 10                              | 22                              | 42                              | 19 | 8,1 | 45 |
| K2218.14513 | offset upwards   | 13                              | 25                              | 45                              | 19 | 8,1 | 45 |
| K2218.14514 | offset upwards   | 14                              | 26                              | 46                              | 19 | 8,1 | 45 |
| K2218.14516 | offset upwards   | 16                              | 28                              | 48                              | 19 | 8,1 | 45 |
| K2218.14518 | straight         | 18                              | 30                              | 50                              | 19 | 8,1 | 45 |
| K2218.14520 | offset downwards | 20                              | 32                              | 52                              | 19 | 8,1 | 45 |
| K2218.14522 | offset downwards | 22                              | 34                              | 54                              | 19 | 8,1 | 45 |
| K2218.14524 | offset downwards | 24                              | 36                              | 56                              | 19 | 8,1 | 45 |
| K2218.14526 | offset downwards | 26                              | 38                              | 58                              | 19 | 8,1 | 45 |
| K2218.14528 | offset downwards | 28                              | 40                              | 60                              | 19 | 8,1 | 45 |
| K2218.14530 | offset downwards | 30                              | 42                              | 62                              | 19 | 8,1 | 45 |
| K2218.14532 | offset downwards | 32                              | 44                              | 64                              | 19 | 8,1 | 45 |
| K2218.14534 | offset downwards | 34                              | 46                              | 66                              | 19 | 8,1 | 45 |
| K2218.14536 | offset downwards | 36                              | 48                              | 68                              | 19 | 8,1 | 45 |
| K2218.14538 | offset downwards | 38                              | 50                              | 70                              | 19 | 8,1 | 45 |
| K2218.14540 | offset downwards | 40                              | 52                              | 72                              | 19 | 8,1 | 45 |
| K2218.14542 | offset downwards | 42                              | 54                              | 74                              | 19 | 8,1 | 45 |