

Ball chains

Item description/product images



Description

Material:

A: Chain brass or stainless steel.

B: Chain brass or stainless steel, key ring stainless steel.

C: Chain brass, ring 1.4310 stainless steel.

Note:

If no length is specified 1000 mm will be supplied.


Drawing reference:

1) same parts


Form A: ball chain, single

Form B: ball chain with key ring

Form C: ball chain with ring clip



Drawings



Overview of items

Form A, ball chains single

Order No.	Form	Version 1	Main material	L	D	D1
K1125.00X160	A	single	brass	160	-	-
K1125.00X320	A	single	brass	320	-	-
K1125.00X500	A	single	brass	500	-	-

Overview of items

Order No.	Form	Version 1	Main material	L	D	D1
K1125.00X1000	A	single	brass	1000	-	-
K1125.01X160	A	single	stainless steel	160	-	-
K1125.01X320	A	single	stainless steel	320	-	-
K1125.01X500	A	single	stainless steel	500	-	-
K1125.01X1000	A	single	stainless steel	1000	-	-
K1125.015X160	B	with key ring	brass	160	15	1
K1125.019X160	B	with key ring	brass	160	19	1
K1125.023X160	B	with key ring	brass	160	23	1,2
K1125.028X160	B	with key ring	brass	160	28	1,7
K1125.015X320	B	with key ring	brass	320	15	1
K1125.019X320	B	with key ring	brass	320	19	1
K1125.023X320	B	with key ring	brass	320	23	1,2
K1125.028X320	B	with key ring	brass	320	28	1,7
K1125.015X500	B	with key ring	brass	500	15	1
K1125.019X500	B	with key ring	brass	500	19	1
K1125.023X500	B	with key ring	brass	500	23	1,2
K1125.028X500	B	with key ring	brass	500	28	1,7
K1125.015X1000	B	with key ring	brass	1000	15	1
K1125.019X1000	B	with key ring	brass	1000	19	1
K1125.023X1000	B	with key ring	brass	1000	23	1,2
K1125.028X1000	B	with key ring	brass	1000	28	1,7
K1125.115X160	B	with key ring	stainless steel	160	15	1
K1125.119X160	B	with key ring	stainless steel	160	19	1
K1125.123X160	B	with key ring	stainless steel	160	23	1,2
K1125.128X160	B	with key ring	stainless steel	160	28	1,7
K1125.115X320	B	with key ring	stainless steel	320	15	1
K1125.119X320	B	with key ring	stainless steel	320	19	1
K1125.123X320	B	with key ring	stainless steel	320	23	1,2
K1125.128X320	B	with key ring	stainless steel	320	28	1,7
K1125.115X500	B	with key ring	stainless steel	500	15	1
K1125.119X500	B	with key ring	stainless steel	500	19	1
K1125.123X500	B	with key ring	stainless steel	500	23	1,2
K1125.128X500	B	with key ring	stainless steel	500	28	1,7
K1125.115X1000	B	with key ring	stainless steel	1000	15	1
K1125.119X1000	B	with key ring	stainless steel	1000	19	1
K1125.123X1000	B	with key ring	stainless steel	1000	23	1,2
K1125.128X1000	B	with key ring	stainless steel	1000	28	1,7
K1125.09X160	C	with ring clip	brass	160	9	1
K1125.09X320	C	with ring clip	brass	320	9	1
K1125.09X500	C	with ring clip	brass	500	9	1
K1125.09X1000	C	with ring clip	brass	1000	9	1
K1125.12X160	C	with ring clip	brass	160	12	1,2
K1125.12X320	C	with ring clip	brass	320	12	1,2
K1125.12X500	C	with ring clip	brass	500	12	1,2
K1125.12X1000	C	with ring clip	brass	1000	12	1,2
K1125.14X160	C	with ring clip	brass	160	14	1,6
K1125.14X320	C	with ring clip	brass	320	14	1,6
K1125.14X500	C	with ring clip	brass	500	14	1,6
K1125.14X1000	C	with ring clip	brass	1000	14	1,6
K1125.16X160	C	with ring clip	brass	160	16	1,6
K1125.16X320	C	with ring clip	brass	320	16	1,6
K1125.16X500	C	with ring clip	brass	500	16	1,6
K1125.16X1000	C	with ring clip	brass	1000	16	1,6
K1125.20X160	C	with ring clip	brass	160	20	2
K1125.20X320	C	with ring clip	brass	320	20	2
K1125.20X500	C	with ring clip	brass	500	20	2
K1125.20X1000	C	with ring clip	brass	1000	20	2
K1125.24X160	C	with ring clip	brass	160	24	2
K1125.24X320	C	with ring clip	brass	320	24	2
K1125.24X500	C	with ring clip	brass	500	24	2
K1125.24X1000	C	with ring clip	brass	1000	24	2
K1125.30X160	C	with ring clip	brass	160	30	2,6

Ball chains

Overview of items

Order No.	Form	Version 1	Main material	L	D	D1
K1125.30X320	C	with ring clip	brass	320	30	2,6
K1125.30X500	C	with ring clip	brass	500	30	2,6
K1125.30X1000	C	with ring clip	brass	1000	30	2,6
K1125.36X160	C	with ring clip	brass	160	36	2,6
K1125.36X320	C	with ring clip	brass	320	36	2,6
K1125.36X500	C	with ring clip	brass	500	36	2,6
K1125.36X1000	C	with ring clip	brass	1000	36	2,6