

Latches adjustable fastening holes covered



Item description/product images



Description

Material:

Steel or stainless steel 1.4301.

Version:

Steel trivalent blue passivated. Stainless steel bright.

Note:

Adjustable latches are secure locking systems for industrial applications. By exceeding the dead center they resist vibration. These latches are very robust and have a low overall height.

After the hook is engaged with the catch plate, the parts to be locked can be drawn together by up to 6 mm by pushing the lever down. To compensate for tolerances or to create enough tension, the hook length can be adjusted using the M6 threaded spindle.

The latches can be screwed down or riveted.

Order required catch plate separately.

The retaining force F1 applies to the latch, not the catch plate.

Drawing reference:

Form A standard Form B with lock Form C with padlock hole


1) Hole arrangement for assembly with catch plate





Latches adjustable fastening holes covered





Drawings











Overview of items

Latches adjustable, fastening holes covered



Latches adjustable fastening holes covered



Overview of items

Order No.	Main material	Form	Retaining force F1 N
K0049.1631161	steel	A	4000
K0049.1631162	stainless steel	Α	4000
K0049.2631161	steel	В	4000
K0049.2631162	stainless steel	В	4000
K0049.3631161	steel	С	4000
K0049.3631162	stainless steel	С	4000
K0048.9163281	steel	Α	-
K0048.9163282	stainless steel	Α	-