

Pneumatic clamps vertical heavy-duty version

Item description/product images



Description

Material:

Steel.

Version:

Black oxidised. Cylinder painted.

On request:


Proximity reed switch.

Pneumatic cylinder:

Double-acting with adjustable end of stroke dampening both ways.

Pneumatic clamps vertical heavy-duty version

Drawings



Overview of items

Pneumatic clamps vertical, heavy-duty version

Order No.	Air consumption per cycle	Opening angle of holding arm	Holding force at 6 bar F1 N	Holding force at 6 bar F2 N	Clamping force at 6 bar F3 N	Clamping force at 6 bar F4 N
K0091.0750	0,27 dm ³	120°	3000	7500	2250	3150
K0091.1750	0,75 dm ³	120°	6500	17500	6500	8000

Pneumatic clamps vertical heavy-duty version

Overview of items

Order No.	A	A1	B	B1	B2	B3	C	C1	C3	D	H	L	L1	L2	S	R	P=Operating pressure bar	strokes per min. at 6 bar
K0091.0750	48	63,5	48	63,5	92,5	12,7	72	19	43	8,7	425	169	67	105	8	G1/4	2 - 6	30
K0091.1750	54,9	76,2	61,8	83	108,7	16	71	25,3	52	10,6	495,6	219	90	129	9,6	G 3/8	2 - 6	15