

Grub screws with flat point hexagon socket DIN EN ISO 4026

Item description/product images

KIPLock



Description

Material:

Steel or stainless steel (A 2).

Thread lock nylon.

Version:


Steel class 45 H, black.

Stainless steel A2-70, bright.

Drawing reference:

L2 = approx. 2x thread pitch

Drawings



Overview of items

Grub screws with flat point, hexagon socket DIN EN ISO 4026

Order No.	Version 2	Main material	L	L1	D1	D2	SW
K0707.03X5	-	steel	5	-	M3	2	1,5
K0707.03X6	-	steel	6	-	M3	2	1,5
K0707.03X8	-	steel	8	-	M3	2	1,5
K0707.03X10	-	steel	10	-	M3	2	1,5
K0707.03X12	-	steel	12	-	M3	2	1,5
K0707.03X16	-	steel	16	-	M3	2	1,5
K0707.03X20	-	steel	20	-	M3	2	1,5
K0707.04X5	-	steel	5	-	M4	2,5	2
K0707.04X6	-	steel	6	-	M4	2,5	2
K0707.04X8	-	steel	8	-	M4	2,5	2
K0707.04X10	-	steel	10	-	M4	2,5	2
K0707.04X12	-	steel	12	-	M4	2,5	2
K0707.04X16	-	steel	16	-	M4	2,5	2
K0707.04X20	-	steel	20	-	M4	2,5	2
K0707.04X25	-	steel	25	-	M4	2,5	2
K0707.05X5	-	steel	5	-	M5	3,5	2,5
K0707.05X6	-	steel	6	-	M5	3,5	2,5
K0707.05X8	-	steel	8	-	M5	3,5	2,5
K0707.05X10	-	steel	10	-	M5	3,5	2,5
K0707.05X12	-	steel	12	-	M5	3,5	2,5
K0707.05X16	-	steel	16	-	M5	3,5	2,5
K0707.05X20	-	steel	20	-	M5	3,5	2,5
K0707.05X25	-	steel	25	-	M5	3,5	2,5
K0707.05X30	-	steel	30	-	M5	3,5	2,5
K0707.06X6	-	steel	6	-	M6	4	3
K0707.06X8	-	steel	8	-	M6	4	3

Grub screws with flat point hexagon socket DIN EN ISO 4026

Overview of items

Order No.	Version 2	Main material	L	L1	D1	D2	SW
K0707.06X10	-	steel	10	-	M6	4	3
K0707.06X12	-	steel	12	-	M6	4	3
K0707.06X16	-	steel	16	-	M6	4	3
K0707.06X20	-	steel	20	-	M6	4	3
K0707.06X25	-	steel	25	-	M6	4	3
K0707.06X30	-	steel	30	-	M6	4	3
K0707.06X35	-	steel	35	-	M6	4	3
K0707.06X40	-	steel	40	-	M6	4	3
K0707.06X45	-	steel	45	-	M6	4	3
K0707.06X50	-	steel	50	-	M6	4	3
K0707.06X60	-	steel	60	-	M6	4	3
K0707.08X8	-	steel	8	-	M8	5,5	4
K0707.08X10	-	steel	10	-	M8	5,5	4
K0707.08X12	-	steel	12	-	M8	5,5	4
K0707.08X16	-	steel	16	-	M8	5,5	4
K0707.08X20	-	steel	20	-	M8	5,5	4
K0707.08X25	-	steel	25	-	M8	5,5	4
K0707.08X30	-	steel	30	-	M8	5,5	4
K0707.08X35	-	steel	35	-	M8	5,5	4
K0707.08X40	-	steel	40	-	M8	5,5	4
K0707.08X45	-	steel	45	-	M8	5,5	4
K0707.08X50	-	steel	50	-	M8	5,5	4
K0707.08X60	-	steel	60	-	M8	5,5	4
K0707.08X70	-	steel	70	-	M8	5,5	4
K0707.08X80	-	steel	80	-	M8	5,5	4
K0707.10X10	-	steel	10	-	M10	7	5
K0707.10X12	-	steel	12	-	M10	7	5
K0707.10X16	-	steel	16	-	M10	7	5
K0707.10X20	-	steel	20	-	M10	7	5
K0707.10X25	-	steel	25	-	M10	7	5
K0707.10X30	-	steel	30	-	M10	7	5
K0707.10X35	-	steel	35	-	M10	7	5
K0707.10X40	-	steel	40	-	M10	7	5
K0707.10X45	-	steel	45	-	M10	7	5
K0707.10X50	-	steel	50	-	M10	7	5
K0707.10X60	-	steel	60	-	M10	7	5
K0707.10X70	-	steel	70	-	M10	7	5
K0707.10X80	-	steel	80	-	M10	7	5
K0707.10X90	-	steel	90	-	M10	7	5
K0707.10X100	-	steel	100	-	M10	7	5
K0707.103X5	-	stainless steel	5	-	M3	2	1,5
K0707.103X6	-	stainless steel	6	-	M3	2	1,5
K0707.103X8	-	stainless steel	8	-	M3	2	1,5
K0707.103X10	-	stainless steel	10	-	M3	2	1,5
K0707.103X12	-	stainless steel	12	-	M3	2	1,5
K0707.104X5	-	stainless steel	5	-	M4	2,5	2
K0707.104X6	-	stainless steel	6	-	M4	2,5	2
K0707.104X8	-	stainless steel	8	-	M4	2,5	2
K0707.104X10	-	stainless steel	10	-	M4	2,5	2
K0707.104X12	-	stainless steel	12	-	M4	2,5	2
K0707.104X16	-	stainless steel	16	-	M4	2,5	2
K0707.104X20	-	stainless steel	20	-	M4	2,5	2
K0707.105X5	-	stainless steel	5	-	M5	3,5	2,5
K0707.105X6	-	stainless steel	6	-	M5	3,5	2,5
K0707.105X8	-	stainless steel	8	-	M5	3,5	2,5
K0707.105X10	-	stainless steel	10	-	M5	3,5	2,5
K0707.105X12	-	stainless steel	12	-	M5	3,5	2,5
K0707.105X16	-	stainless steel	16	-	M5	3,5	2,5
K0707.105X20	-	stainless steel	20	-	M5	3,5	2,5
K0707.105X25	-	stainless steel	25	-	M5	3,5	2,5
K0707.105X30	-	stainless steel	30	-	M5	3,5	2,5
K0707.106X6	-	stainless steel	6	-	M6	4	3

Grub screws with flat point hexagon socket DIN EN ISO 4026

Overview of items

Order No.	Version 2	Main material	L	L1	D1	D2	SW
K0707.106X8	-	stainless steel	8	-	M6	4	3
K0707.106X10	-	stainless steel	10	-	M6	4	3
K0707.106X12	-	stainless steel	12	-	M6	4	3
K0707.106X16	-	stainless steel	16	-	M6	4	3
K0707.106X20	-	stainless steel	20	-	M6	4	3
K0707.106X25	-	stainless steel	25	-	M6	4	3
K0707.106X30	-	stainless steel	30	-	M6	4	3
K0707.106X35	-	stainless steel	35	-	M6	4	3
K0707.106X40	-	stainless steel	40	-	M6	4	3
K0707.108X8	-	stainless steel	8	-	M8	5,5	4
K0707.108X10	-	stainless steel	10	-	M8	5,5	4
K0707.108X12	-	stainless steel	12	-	M8	5,5	4
K0707.108X16	-	stainless steel	16	-	M8	5,5	4
K0707.108X20	-	stainless steel	20	-	M8	5,5	4
K0707.108X25	-	stainless steel	25	-	M8	5,5	4
K0707.108X30	-	stainless steel	30	-	M8	5,5	4
K0707.108X35	-	stainless steel	35	-	M8	5,5	4
K0707.108X40	-	stainless steel	40	-	M8	5,5	4
K0707.108X45	-	stainless steel	45	-	M8	5,5	4
K0707.108X50	-	stainless steel	50	-	M8	5,5	4
K0707.110X10	-	stainless steel	10	-	M10	7	5
K0707.110X12	-	stainless steel	12	-	M10	7	5
K0707.110X16	-	stainless steel	16	-	M10	7	5
K0707.110X20	-	stainless steel	20	-	M10	7	5
K0707.110X25	-	stainless steel	25	-	M10	7	5
K0707.110X30	-	stainless steel	30	-	M10	7	5
K0707.110X35	-	stainless steel	35	-	M10	7	5
K0707.110X40	-	stainless steel	40	-	M10	7	5
K0707.110X45	-	stainless steel	45	-	M10	7	5
K0707.110X50	-	stainless steel	50	-	M10	7	5
K0707.203X5	with thread lock	steel	5	2	M3	2	1,5
K0707.203X6	with thread lock	steel	6	3	M3	2	1,5
K0707.203X8	with thread lock	steel	8	4	M3	2	1,5
K0707.203X10	with thread lock	steel	10	4	M3	2	1,5
K0707.203X12	with thread lock	steel	12	4	M3	2	1,5
K0707.204X5	with thread lock	steel	5	2	M4	2,5	2
K0707.204X6	with thread lock	steel	6	2,5	M4	2,5	2
K0707.204X8	with thread lock	steel	8	3,5	M4	2,5	2
K0707.204X10	with thread lock	steel	10	5	M4	2,5	2
K0707.204X12	with thread lock	steel	12	5	M4	2,5	2
K0707.204X16	with thread lock	steel	16	5	M4	2,5	2
K0707.205X5	with thread lock	steel	5	2	M5	3,5	2,5
K0707.205X6	with thread lock	steel	6	3	M5	3,5	2,5
K0707.205X8	with thread lock	steel	8	3,5	M5	3,5	2,5
K0707.205X10	with thread lock	steel	10	3,5	M5	3,5	2,5
K0707.205X12	with thread lock	steel	12	5	M5	3,5	2,5
K0707.205X16	with thread lock	steel	16	6	M5	3,5	2,5
K0707.206X6	with thread lock	steel	6	2,5	M6	4	3
K0707.206X8	with thread lock	steel	8	3	M6	4	3
K0707.206X10	with thread lock	steel	10	3,5	M6	4	3
K0707.206X12	with thread lock	steel	12	5	M6	4	3
K0707.206X16	with thread lock	steel	16	7	M6	4	3
K0707.206X20	with thread lock	steel	20	7	M6	4	3
K0707.208X8	with thread lock	steel	8	3	M8	5,5	4
K0707.208X10	with thread lock	steel	10	3,5	M8	5,5	4
K0707.208X12	with thread lock	steel	12	5	M8	5,5	4
K0707.208X16	with thread lock	steel	16	8	M8	5,5	4
K0707.208X20	with thread lock	steel	20	8	M8	5,5	4
K0707.210X10	with thread lock	steel	10	5	M10	7	5
K0707.210X12	with thread lock	steel	12	5	M10	7	5
K0707.210X16	with thread lock	steel	16	9	M10	7	5
K0707.210X20	with thread lock	steel	20	9	M10	7	5

Grub screws with flat point hexagon socket DIN EN ISO 4026

Overview of items

Order No.	Version 2	Main material	L	L1	D1	D2	SW
K0707.303X5	with thread lock	stainless steel	5	2	M3	2	1,5
K0707.303X6	with thread lock	stainless steel	6	3	M3	2	1,5
K0707.303X8	with thread lock	stainless steel	8	4	M3	2	1,5
K0707.303X10	with thread lock	stainless steel	10	4	M3	2	1,5
K0707.303X12	with thread lock	stainless steel	12	4	M3	2	1,5
K0707.304X5	with thread lock	stainless steel	5	2	M4	2,5	2
K0707.304X6	with thread lock	stainless steel	6	2,5	M4	2,5	2
K0707.304X8	with thread lock	stainless steel	8	3,5	M4	2,5	2
K0707.304X10	with thread lock	stainless steel	10	5	M4	2,5	2
K0707.304X12	with thread lock	stainless steel	12	5	M4	2,5	2
K0707.304X16	with thread lock	stainless steel	16	5	M4	2,5	2
K0707.305X5	with thread lock	stainless steel	5	2	M5	3,5	2,5
K0707.305X6	with thread lock	stainless steel	6	3	M5	3,5	2,5
K0707.305X8	with thread lock	stainless steel	8	3,5	M5	3,5	2,5
K0707.305X10	with thread lock	stainless steel	10	3,5	M5	3,5	2,5
K0707.305X12	with thread lock	stainless steel	12	5	M5	3,5	2,5
K0707.305X16	with thread lock	stainless steel	16	6	M5	3,5	2,5
K0707.306X6	with thread lock	stainless steel	6	2,5	M6	4	3
K0707.306X8	with thread lock	stainless steel	8	3	M6	4	3
K0707.306X10	with thread lock	stainless steel	10	3,5	M6	4	3
K0707.306X12	with thread lock	stainless steel	12	5	M6	4	3
K0707.306X16	with thread lock	stainless steel	16	7	M6	4	3
K0707.308X8	with thread lock	stainless steel	8	3	M8	5,5	4
K0707.306X20	with thread lock	stainless steel	20	7	M6	4	3
K0707.308X10	with thread lock	stainless steel	10	3,5	M8	5,5	4
K0707.308X12	with thread lock	stainless steel	12	5	M8	5,5	4
K0707.308X16	with thread lock	stainless steel	16	8	M8	5,5	4
K0707.308X20	with thread lock	stainless steel	20	8	M8	5,5	4
K0707.310X10	with thread lock	stainless steel	10	5	M10	7	5
K0707.310X12	with thread lock	stainless steel	12	5	M10	7	5
K0707.310X16	with thread lock	stainless steel	16	9	M10	7	5
K0707.310X20	with thread lock	stainless steel	20	9	M10	7	5