

Swivel castors

Item description/product images



Description

Material:

Housing and wheel rim steel plate.

Tyres solid rubber.

Wheel hub steel tube.

Version:

Housing and rim press formed.

Double ball bearing with ball shield in castor head.


Roller bearings in the wheels.

Note:


Wheel axle bolted.

Drawings

swivel castor



Drawings



Overview of items

Order No.	Version 1	Wheel bearing	A	B	B1	B2	B3	D	D1	L	L1	H	R	Permissible load kg
K1761.08025	without locking system	roller bearing	38	25	-	60	85	80	9	100	80	102	78	50
K1761.10030	without locking system	roller bearing	36	30	-	60	85	100	9	100	80	125	86	70
K1761.12538	without locking system	roller bearing	40	37,5	-	60	85	125	9	100	80	150	102,5	100
K1761.16040	without locking system	roller bearing	60	40	75	80	110	160	11	140	105	195	140	135
K1761.20050	without locking system	roller bearing	65	50	75	80	110	200	11	140	105	235	165	205