

Tension levers, stainless steel, with reamed hole, 0 degrees

Item description/product images



Description

Material:

Steel parts stainless steel 1.4305.

Ball knob black plastic.

Version:

Stainless steel parts bright.

Ball knob polished.

Note:

Tension levers can be used for simple clamping or control operations.

Where applicable, there must be enough space available so that the grip can be rotated 360°.

Overview of items

| Order No. | Thread type | Form | Size | X | T | D | D1 | D2 | H | H1 | H2 | A | A2 |
|------------|-------------|------|------|----|----|----|----|----|----|----|------|-------|----|
| K1444.1102 | reamed hole | 0° | 1 | 10 | 22 | 24 | 10 | 25 | 40 | - | 32,5 | 88,1 | - |
| K1444.1122 | reamed hole | 0° | 2 | 12 | 25 | 28 | 12 | 32 | 46 | - | 36,5 | 104 | - |
| K1444.1142 | reamed hole | 0° | 2 | 14 | 25 | 28 | 12 | 32 | 46 | - | 36,5 | 104 | - |
| K1444.1162 | reamed hole | 0° | 3 | 16 | 28 | 33 | 13 | 32 | 52 | - | 41 | 126,5 | - |
| K1444.1202 | reamed hole | 0° | 4 | 20 | 32 | 41 | 13 | 32 | 61 | - | 49 | 128,5 | - |