

Fixed castors

Item description/product images



Description

Material:

Housing, steel plate.

Wheel tyre, high-quality elastic solid rubber.

Wheel rim, high-quality unbreakable polyamide or die-cast aluminium.

Version:

Housing, press-formed.

Swivel housing, double-row ball bearings in a swivel head.

Ball bearing wheel axle bearings.

Note:

Wheel axle bolted.

Swivel and fixed castors with mounting plate.

Application:


Heavy loads can be easily transported using this load handling equipment. The roll and swivel resistance is reduced with this new wheel series designed for intralogistic heavy load applications.

Temperature range:

-25 °C to +70 °C

Drawings

fixed castor



Fixed castors

Overview of items

Order No.	Item	Wheel bearing	B	B1	B2	B3	D	D1	H	L	L1	L2	Permissible load kg
K1765.101000401	Fixed castor	ball bearing	40	60	55	85	100	9	125	100	80	76	200
K1765.101250401	Fixed castor	ball bearing	40	60	55	85	125	9	150	100	80	76	200
K1765.101500501	Fixed castor	ball bearing	50	80	75	110	150	11	190	140	105	-	400
K1765.101600501	Fixed castor	ball bearing	50	80	75	110	160	11	195	140	105	-	400
K1765.102000501	Fixed castor	ball bearing	50	80	75	110	200	11	235	140	105	-	400