

Swivel castors with stop fix

Item description/product images



Description

Material:

Housing, steel plate.

Wheel tread, high quality polyurethane elastomere.

Wheel rims, die-cast aluminium.

Version:

Housing, press-formed.

Swivel housing, double-row ball bearings in a swivel head.

Ball bearing wheel axle bearings.

Note:

Wheel axle bolted.

Swivel and fixed castors with mounting plate.

Application:


Heavy loads can be easily transported using this load handling equipment. The roll and swivel resistance is reduced with this new wheel series designed for intralogistic heavy load applications.

Temperature range:

-25 °C to +70 °C

Drawings

swivel castor
with "stop-fix"



swivel head bearing:

Swivel castors with stop fix

Overview of items

Order No.	Item	Wheel bearing	A	B	B1	B2	B3	D	D1	H	L	L1	L2	R	Permissible load kg
K1765.101000402	Swivel castor	ball bearing	36	40	60	55	85	100	9	125	100	80	76	86	200
K1765.101250402	Swivel castor	ball bearing	40	40	60	55	85	125	9	150	100	80	76	102,5	200
K1765.101500502	Swivel castor	ball bearing	60	50	80	75	110	150	11	190	140	105	-	135	400
K1765.101600502	Swivel castor	ball bearing	60	50	80	75	110	160	11	195	140	105	-	140	400
K1765.102000502	Swivel castor	ball bearing	65	50	80	75	110	200	11	235	140	105	-	165	400