

Washers for clamps DIN 6340

Item description/product images



Description

Material:


Steel or EN AW-7022

Version:


Stamped steel: pressed flat and tempered to 1200-1400 N/mm², black.

Turned steel: black oxidised.

Turned aluminium: anodised.



Drawings



Overview of items

Heavy-duty washers DIN 6340

Order No.	Material	D1	D2	H	for bolt
K0867.06	steel	6,4	17	3	M6
K0867.08	steel	8,4	23	4	M8
K0867.10	steel	10,5	28	4	M10
K0867.12	steel	13	35	5	M12
K0867.14	steel	15	40	5	M14
K0867.22	steel	23	50	5,6	M22
K0867.16	steel	17	45	6	M16
K0867.18	steel	19	45	6	M18
K0867.20	steel	21	50	6	M20
K0867.24	steel	25	60	8	M24

Washers for clamps DIN 6340

Overview of items

Order No.	Material	D1	D2	H	for bolt
K0867.30	steel	31	68	10	M30
K0867.36	steel	38	80	10	M36
K0867.206	Aluminium	6,4	17	3	M6
K0867.208	Aluminium	8,4	23	4	M8
K0867.210	Aluminium	10,5	28	4	M10
K0867.212	Aluminium	13	35	5	M12
K0867.214	Aluminium	15	40	5	M14
K0867.216	Aluminium	17	45	6	M16
K0867.218	Aluminium	19	45	6	M18
K0867.220	Aluminium	21	50	6	M20
K0867.222	Aluminium	23	50	8	M22
K0867.224	Aluminium	25	60	8	M24
K0867.230	Aluminium	31	68	10	M30
K0867.236	Aluminium	38	80	10	M36
K0867.306	steel turned	6,4	17	3	M6
K0867.308	steel turned	8,4	23	4	M8
K0867.310	steel turned	10,5	28	4	M10
K0867.312	steel turned	13	35	5	M12
K0867.314	steel turned	15	40	5	M14
K0867.316	steel turned	17	45	6	M16
K0867.318	steel turned	19	45	6	M18
K0867.320	steel turned	21	50	6	M20