


Washers medium, DIN EN ISO 7089 A

Item description/product images



Description

Material:

Steel, stainless steel A2 or stainless steel A4.


Version:

Steel, bright.

Stainless steel A2, bright.

Stainless steel A4, bright.

Drawings



Overview of items

Medium washers DIN EN ISO 7089 A

Order No.	Main material	Grade	for screws	D1	D2	H
K0868.03	0.0048	-	M3	3,2	7	0,5
K0868.04	0.0048	-	M4	4,3	9	0,8
K0868.05	0.0048	-	M5	5,3	10	1
K0868.06	0.0048	-	M6	6,4	12	1,6
K0868.08	0.0048	-	M8	8,4	16	1,6
K0868.10	0.0048	-	M10	10,5	20	2
K0868.12	0.0048	-	M12	13	24	2,5
K0868.14	0.0048	-	M14	15	28	2,5
K0868.16	0.0048	-	M16	17	30	3
K0868.20	0.0048	-	M20	21	37	3
K0868.24	0.0048	-	M24	25	44	4
K0868.30	0.0048	-	M30	31	56	4

Washers medium, DIN EN ISO 7089 A

Overview of items

Order No.	Main material	Grade	for screws	D1	D2	H
K0868.36	0.0048	-	M36	37	66	5
K0868.103	additional carriage for concentricity gauge 32506	70	M3	3,2	7	0,5
K0868.104	additional carriage for concentricity gauge 32506	70	M4	4,3	9	0,8
K0868.105	additional carriage for concentricity gauge 32506	70	M5	5,3	10	1
K0868.106	additional carriage for concentricity gauge 32506	70	M6	6,4	12	1,6
K0868.108	additional carriage for concentricity gauge 32506	70	M8	8,4	16	1,6
K0868.110	additional carriage for concentricity gauge 32506	70	M10	10,5	20	2
K0868.112	additional carriage for concentricity gauge 32506	70	M12	13	24	2,5
K0868.114	additional carriage for concentricity gauge 32506	70	M14	15	28	2,5
K0868.116	additional carriage for concentricity gauge 32506	70	M16	17	30	3
K0868.120	additional carriage for concentricity gauge 32506	70	M20	21	37	3
K0868.124	additional carriage for concentricity gauge 32506	70	M24	25	44	4
K0868.130	additional carriage for concentricity gauge 32506	70	M30	31	56	4
K0868.136	additional carriage for concentricity gauge 32506	70	M36	37	66	5
K0868.603	Clamping width 50 mm, width approx. 20 mm	70	M3	3,2	7	0,5
K0868.604	Clamping width 50 mm, width approx. 20 mm	70	M4	4,3	9	0,8
K0868.605	Clamping width 50 mm, width approx. 20 mm	70	M5	5,3	10	1
K0868.606	Clamping width 50 mm, width approx. 20 mm	70	M6	6,4	12	1,6
K0868.608	Clamping width 50 mm, width approx. 20 mm	70	M8	8,4	16	1,6
K0868.610	Clamping width 50 mm, width approx. 20 mm	70	M10	10,5	20	2
K0868.612	Clamping width 50 mm, width approx. 20 mm	70	M12	13	24	2,5
K0868.614	Clamping width 50 mm, width approx. 20 mm	70	M14	15	28	2,5
K0868.616	Clamping width 50 mm, width approx. 20 mm	70	M16	17	30	3
K0868.620	Clamping width 50 mm, width approx. 20 mm	70	M20	21	37	3
K0868.624	Clamping width 50 mm, width approx. 20 mm	70	M24	25	44	4
K0868.630	Clamping width 50 mm, width approx. 20 mm	70	M30	31	56	4
K0868.636	Clamping width 50 mm, width approx. 20 mm	70	M36	37	66	5