

Knurled knobs

Item description/product images



black grey RAL 7021	pure orange RAL 2004	signal green RAL 6032	traffic blue RAL 5017
light grey RAL 7035	traffic red RAL 3020	colza yellow RAL 1021	

Description

Material:

Thermoplastic, black grey.
Bush steel.

Version:

Bush blue passivated

Note:

Available without graduations, with one scale line or with 20 graduations and 10 digits.

Δ Add the desired cap colour here. No colour code is required for black grey caps.

On request:

Special graduations.

Drawing reference:


Form A: without graduations

Form B: with one scale line

Form C: with standard graduations

1) Set screw for locking (by Form C between numbers 5 and 6)

Drawings



Overview of items

Knurled knobs

Order No.	Form	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	T
K0248.1105	A	black grey RAL 7021	5	21	19	19	M3	22	10,5	5	10
K0248.11051	A	orange RAL 2004	5	21	19	19	M3	22	10,5	5	10
K0248.11052	A	signal green RAL 6032	5	21	19	19	M3	22	10,5	5	10
K0248.11053	A	blue RAL 5017	5	21	19	19	M3	22	10,5	5	10
K0248.11055	A	light grey RAL 7035	5	21	19	19	M3	22	10,5	5	10
K0248.11056	A	traffic red RAL 3020	5	21	19	19	M3	22	10,5	5	10

Overview of items

Order No.	Form	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	T
K0248.11057	A	colza yellow RAL 1021	5	21	19	19	M3	22	10,5	5	10
K0248.1206	A	black grey RAL 7021	6	26	23	23	M3	26	12	6	10
K0248.12061	A	orange RAL 2004	6	26	23	23	M3	26	12	6	10
K0248.12062	A	signal green RAL 6032	6	26	23	23	M3	26	12	6	10
K0248.12063	A	blue RAL5017	6	26	23	23	M3	26	12	6	10
K0248.12065	A	light grey RAL 7035	6	26	23	23	M3	26	12	6	10
K0248.12066	A	traffic red RAL 3020	6	26	23	23	M3	26	12	6	10
K0248.12067	A	colza yellow RAL 1021	6	26	23	23	M3	26	12	6	10
K0248.1308	A	black grey RAL 7021	8	34	31	31	M4	36	17,5	7	14
K0248.13081	A	orange RAL 2004	8	34	31	31	M4	36	17,5	7	14
K0248.13082	A	signal green RAL 6032	8	34	31	31	M4	36	17,5	7	14
K0248.13083	A	blue RAL5017	8	34	31	31	M4	36	17,5	7	14
K0248.13085	A	light grey RAL 7035	8	34	31	31	M4	36	17,5	7	14
K0248.13086	A	traffic red RAL 3020	8	34	31	31	M4	36	17,5	7	14
K0248.13087	A	colza yellow RAL 1021	8	34	31	31	M4	36	17,5	7	14
K0248.3105	C	black grey RAL 7021	5	21	19	19	M3	22	10,5	5	10
K0248.31051	C	orange RAL 2004	5	21	19	19	M3	22	10,5	5	10
K0248.31052	C	signal green RAL 6032	5	21	19	19	M3	22	10,5	5	10
K0248.31053	C	blue RAL5017	5	21	19	19	M3	22	10,5	5	10
K0248.31055	C	light grey RAL 7035	5	21	19	19	M3	22	10,5	5	10
K0248.31056	C	traffic red RAL 3020	5	21	19	19	M3	22	10,5	5	10
K0248.31057	C	colza yellow RAL 1021	5	21	19	19	M3	22	10,5	5	10
K0248.3206	C	black grey RAL 7021	6	26	23	23	M3	26	12	6	10
K0248.32061	C	orange RAL 2004	6	26	23	23	M3	26	12	6	10
K0248.32062	C	signal green RAL 6032	6	26	23	23	M3	26	12	6	10
K0248.32063	C	blue RAL5017	6	26	23	23	M3	26	12	6	10
K0248.32065	C	light grey RAL 7035	6	26	23	23	M3	26	12	6	10
K0248.32066	C	traffic red RAL 3020	6	26	23	23	M3	26	12	6	10
K0248.32067	C	colza yellow RAL 1021	6	26	23	23	M3	26	12	6	10
K0248.3308	C	black grey RAL 7021	8	34	31	31	M4	36	17,5	7	14
K0248.33081	C	orange RAL 2004	8	34	31	31	M4	36	17,5	7	14
K0248.33082	C	signal green RAL 6032	8	34	31	31	M4	36	17,5	7	14
K0248.33083	C	blue RAL5017	8	34	31	31	M4	36	17,5	7	14
K0248.33085	C	light grey RAL 7035	8	34	31	31	M4	36	17,5	7	14
K0248.33086	C	traffic red RAL 3020	8	34	31	31	M4	36	17,5	7	14
K0248.33087	C	colza yellow RAL 1021	8	34	31	31	M4	36	17,5	7	14