

Fixed castors

Item description/product images



Description

Material:

Housing steel plate.

Wheel body die-cast aluminium with Extrathane® tread.

Version:

Pressed housing; wheels with precision ball bearing


Note:

The wheels are corrosion resistant and they have a low rolling resistance. Wheel axle bolted.

From diameter 125 mm the wheels have spokes.

Drawings

fixed castor



Overview of items

Order No.	Item	Version 1	Wheel bearing	B	B1	B2	B3	D	D1	H	L	L1	Permissible load kg
K1767.100401	Fixed castor	without locking system	ball bearing	40	60	-	85	100	9	130	100	80	250
K1767.125401	Fixed castor	without locking system	ball bearing	40	60	-	85	125	9	155	100	80	250
K1767.160501	Fixed castor	without locking system	ball bearing	50	80	75	110	160	11	202	140	105	550
K1767.200501	Fixed castor	without locking system	ball bearing	50	80	75	110	200	11	245	140	105	800

