

Chock clamps

Item description/product images



Description

Material:

Clamping element steel or brass.

Version:

Steel hardened.

Note:

Also known as pitbull clamps.

Extremely space-saving design.

No protruding edges due to lateral clamping.


Positive down force.

Drawing reference:

1) workpiece

2) Fixture

Drawings



Overview of items

Chock clamps

Overview of items

Chock clamps

Order No.	Version	Main material	D	B	B1	H	H1	L	Clamping travel	Clamping force kN	Tightening torque max. Nm
K0030.110	for compact swing clamp	0.002	M2,5X8	9,5	3,8	6	3,6	9,5	0,15	2,8	1,8
K0030.113	for compact swing clamp	0.002	M4X12	12,7	5,1	8	4,8	13	0,4	6,6	5,6
K0030.119	for compact swing clamp	0.002	M6X16	19,05	7,6	11,5	7,2	19	0,6	16	22,5
K0030.210	for conical and ball head grease nipples	0.002	M2,5X8	9,5	3,8	6	3,6	9,5	0,15	2,8	1,8
K0030.213	for conical and ball head grease nipples	0.002	M4X12	12,7	5,1	8	4,8	13	0,4	6,6	5,6
K0030.219	for conical and ball head grease nipples	0.002	M6X16	19,05	7,6	11,5	7,2	19	0,6	16	22,5
K0030.310	for conical and ball head grease nipples	560 mm / M10x1.25 / M8	M2,5X8	9,5	3,8	6	3,6	9,5	0,15	0,9	0,56
K0030.313	for conical and ball head grease nipples	560 mm / M10x1.25 / M8	M4X12	12,7	5,1	8	4,8	13	0,4	1,8	2,8
K0030.319	for conical and ball head grease nipples	560 mm / M10x1.25 / M8	M6X16	19,05	7,6	11,5	7,2	19	0,6	4,2	5,6