

## Shaft clamping units

### Item description/product images



### Description

#### Material:

Jaws steel.  
Spring 1.4310.  
Screw grade 8.8.

#### Version:

Jaws black oxidised.  
Screw blue electro zinc-plated.


#### Note:

These shaft clamping units are the simple alternative to conventional shaft clamping (slot and grub screw).

The units are suitable for various materials (metal, plastic, wood etc).

To loosen a jammed clamp simply hit it axially or extract it using a screw in the jaw end or screw head.

### Drawings



## Shaft clamping units

### Overview of items

#### Shaft clamping units

| Order No. | D<br>min. | D<br>max. | D1 | D2 | D3  | G   | G1   | H  | L<br>max. | L1 | SW | X   | Clamping torque Mx<br>Nm | Tightening<br>torque<br>max. Nm | Order No.<br>assembly<br>tool |
|-----------|-----------|-----------|----|----|-----|-----|------|----|-----------|----|----|-----|--------------------------|---------------------------------|-------------------------------|
| K0375.04  | 6         | 10        | 8  | 8  | M4  | M5  | M2,5 | 4  | 27        | 8  | 3  | 2,8 | max. 20                  | 2,9                             | K0375.904                     |
| K0375.05  | 10        | 15        | 10 | 10 | M5  | M6  | M3   | 5  | 33        | 10 | 4  | 3,3 | max. 45                  | 6                               | K0375.905                     |
| K0375.06  | 15        | 20        | 12 | 12 | M6  | M7  | M4   | 6  | 39        | 12 | 5  | 3,5 | max. 100                 | 10                              | K0375.906                     |
| K0375.08  | 20        | 30        | 16 | 16 | M8  | M10 | M5   | 8  | 46        | 16 | 6  | 4   | max. 170                 | 25                              | K0375.908                     |
| K0375.10  | 30        | 40        | 20 | 20 | M10 | M12 | M6   | 10 | 53        | 20 | 8  | 4,8 | max. 290                 | 46                              | K0375.910                     |
| K0375.12  | 40        | 60        | 25 | 25 | M12 | M14 | M8   | 12 | 70        | 25 | 10 | 5,6 | max. 450                 | 82                              | K0375.912                     |
| K0375.16  | 60        | 125       | 30 | 30 | M16 | M18 | M10  | 16 | 81        | 30 | 14 | 7,9 | max. 650                 | 206                             | K0375.916                     |