

Repair kit

Item description/product images



Description

Material, version:

Threaded insert passivated steel.

Note:

The repair kit allows threaded holes which have been damaged, torn out or jammed to be used again or to be repaired. This makes it possible to recover scrap and rejects of expensive products.

Threaded inserts are suitable for use in various materials, including light metals and casting.

Inserts with internal threads larger than M6 are supplied with four locking pins instead of two.

Permissible deviations:

the medium tolerance class applies to the threads listed, i.e. 6H for nut threads and 6g for bolt threads. Other dimensions ± 0.25 mm.

Technical information see operating instructions for threaded inserts.

Advantages:

- Quick and easy installation.
- The insert is fixed with pins in order to prevent torsion due to twisting or vibrations.
- No other special tools are required besides the assembly tool.

Overview of items

Repair kit

| Order No. | Female threads | Male threads | Insert length | Number of inserts | Number of assembly tools | Order No. of individual insert |
|-----------|----------------|--------------|---------------|-------------------|--------------------------|--------------------------------|
| K0653.01 | M5 | M8 | 8 | 8 | 1 | K0398.05 K0398.06 |
| | M6 | M10X1,25 | 10 | 8 | 1 | K0398.08 K0398.08X1 |
| | M8 | M12X1,25 | 12 | 6 | 1 | K0398.10 K0398.10X125 |
| | M8X1 | M12X1,25 | 12 | 6 | - | K0398.12 K0398.12X125 |
| | M10 | M14X1,5 | 14 | 4 | 1 | |
| | M10X1,25 | M14X1,5 | 14 | 4 | - | |
| | M12 | M16X1,5 | 16 | 3 | 1 | |
| | M12X1,25 | M16X1,5 | 16 | 3 | - | |