

Studs with screw-in stop for gluing in

Item description/product images



Description

Material:

Steel or 1.4305 stainless steel.

Version:

Steel trivalent blue passivated.

Stainless steel, bright.

Note:


Studs with screw-in stop have been designed especially for gluing-in. They allow mechanical connecting elements with external thread to be made cost-effectively for small and medium-sized series.

The LOCTITE products 638 and 648 (see K0655) have proven themselves in practice as successful bonding agents.

Drawing reference:

1) screw-in stop

Drawings



Overview of items

Studs with screw-in stop

Order No.	Main material	D	L	L1	L2
K0404.1040201	steel	M4	20	6	1
K0404.1040301	steel	M4	30	6	1
K0404.1040401	steel	M4	40	6	1
K0404.1040501	steel	M4	50	6	1
K0404.1050201	steel	M5	20	8	1
K0404.1050301	steel	M5	30	8	1
K0404.1050401	steel	M5	40	8	1
K0404.1050501	steel	M5	50	8	1
K0404.1050601	steel	M5	60	8	1
K0404.1060201	steel	M6	20	9	1,5
K0404.1060301	steel	M6	30	9	1,5
K0404.1060401	steel	M6	40	9	1,5
K0404.1060501	steel	M6	50	9	1,5
K0404.1060601	steel	M6	60	9	1,5
K0404.1080201	steel	M8	20	12	1,5
K0404.1080301	steel	M8	30	12	1,5
K0404.1080401	steel	M8	40	12	1,5
K0404.1080501	steel	M8	50	12	1,5

Studs with screw-in stop for gluing in

Overview of items

Order No.	Main material	D	L	L1	L2
K0404.1080601	steel	M8	60	12	1,5
K0404.1080801	steel	M8	80	12	1,5
K0404.1100201	steel	M10	20	14	2
K0404.1100301	steel	M10	30	14	2
K0404.1100401	steel	M10	40	14	2
K0404.1100501	steel	M10	50	14	2
K0404.1100601	steel	M10	60	14	2
K0404.1100801	steel	M10	80	14	2
K0404.1120301	steel	M12	30	17	2
K0404.1120401	steel	M12	40	17	2
K0404.1120501	steel	M12	50	17	2
K0404.1120601	steel	M12	60	17	2
K0404.1120801	steel	M12	80	17	2
K0404.1160301	steel	M16	30	22	2
K0404.1160401	steel	M16	40	22	2
K0404.1160501	steel	M16	50	22	2
K0404.1160601	steel	M16	60	22	2
K0404.1160801	steel	M16	80	22	2
K0404.1040202	stainless steel	M4	20	6	1
K0404.1040302	stainless steel	M4	30	6	1
K0404.1040402	stainless steel	M4	40	6	1
K0404.1040502	stainless steel	M4	50	6	1
K0404.1050202	stainless steel	M5	20	8	1
K0404.1050302	stainless steel	M5	30	8	1
K0404.1050402	stainless steel	M5	40	8	1
K0404.1050502	stainless steel	M5	50	8	1
K0404.1050602	stainless steel	M5	60	8	1
K0404.1060202	stainless steel	M6	20	9	1,5
K0404.1060302	stainless steel	M6	30	9	1,5
K0404.1060402	stainless steel	M6	40	9	1,5
K0404.1060502	stainless steel	M6	50	9	1,5
K0404.1060602	stainless steel	M6	60	9	1,5
K0404.1080202	stainless steel	M8	20	12	1,5
K0404.1080302	stainless steel	M8	30	12	1,5
K0404.1080402	stainless steel	M8	40	12	1,5
K0404.1080502	stainless steel	M8	50	12	1,5
K0404.1080602	stainless steel	M8	60	12	1,5
K0404.1080802	stainless steel	M8	80	12	1,5
K0404.1100202	stainless steel	M10	20	14	2
K0404.1100302	stainless steel	M10	30	14	2
K0404.1100402	stainless steel	M10	40	14	2
K0404.1100502	stainless steel	M10	50	14	2
K0404.1100602	stainless steel	M10	60	14	2
K0404.1100802	stainless steel	M10	80	14	2
K0404.1120302	stainless steel	M12	30	17	2
K0404.1120402	stainless steel	M12	40	17	2
K0404.1120502	stainless steel	M12	50	17	2
K0404.1120602	stainless steel	M12	60	17	2
K0404.1120802	stainless steel	M12	80	17	2
K0404.1160302	stainless steel	M16	30	22	2
K0404.1160402	stainless steel	M16	40	22	2
K0404.1160502	stainless steel	M16	50	22	2
K0404.1160602	stainless steel	M16	60	22	2
K0404.1160802	stainless steel	M16	80	22	2

